






1 MATERIAL: CONNECTOR— NYLON UL94V—2 (ORANGE).
CONTACTS — 0.30 [.012] THK COPPER ALLOY
(PLATED 0.00076 [.000030] MIN GOLD OR 0.00008 [.000003] MIN
GOLD FLASH OVER 0.00068 [.000027] PALLADIUM NICKEL, PER
TE CONNECTIVITY'S DISCRETION, ON POST END, WITH MATTE TIN
0.00203 [.000080] MIN THK ON WIRE END)
OR
CONTACTS — 0.30 [.012] THK COPPER ALLOY
(PLATED 0.00076 [.000030] MIN GOLD OR 0.00008 [.000003] MIN
GOLD FLASH OVER 0.00068 [.000027] PALLADIUM NICKEL, PER
TE CONNECTIVITY'S DISCRETION, ON POST END, WITH MATTE TIN
0.00203 [.000080] MIN THK ON WIRE END)

2 CONTACTS ACCEPT #18 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX INSULATION DIA.

3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.

4 HOUSING FEATURES: CLOSED END.

5 DIMENSIONS IN BRACKETS ARE IN INCHES.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS

4805 (3/11)