

D

C

B


A

D




C

B


A




- ⚠ 0.00127 [.000050] NICKEL PLATE WITH 0.00076 [.000030] GOLD PLATE ON INSIDE OF RECEPTACLE.
2. WIRE RANGE: 0.5–2mm² (20–14 AWG).
3. INSULATION RANGE: 3.56 [.140] MAX. DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.




SECTION A—A
SCALE 10:1




SECTION B—B
SCALE 10:1




SECTION C—C
SCALE 10:1



SECTION D—D
SCALE 10:1



OBSOLETE	— PRE-TIN —	0.25 [.010] PHOS BRZ	770144-6
		0.25 [.010] BRASS	770144-5
	PRE-TIN	0.25 [.010] BRASS	770144-1
	FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19JUN2007	 TE Connectivity	
		CHK C. CASH 19JUN2007		
DIMENSIONS: mm (INCHES)	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. CASH 19JUN2007	NAME	
		PRODUCT SPEC — APPLICATION SPEC	SOCKET, .093, LOOSE PIECE, COMMERCIAL PIN AND SOCKET —	
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -	WEIGHT 0.000000	SIZE	
			CAGE CODE	
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING	DRAWING NO	
			RESTRICTED TO	
			A1 00779 C=770144	SCALE 5:1
				SHEET 1 of 1
				REV F1