








© COPYRIGHT

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			K1	REVISED PER ECO-11-005294	06APR11
					HMR



1. .010 MAX CUT-OFF TAB FOR LOOSE PIECE.
2. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA
3. GOLD FLASH OVER .000050 NICKEL ENTIRE CONTACT .000030 GOLD ON CONTACT AREA.
4. .000016 MIN TIN.
5. LUBRICATED
6. .000100-.000200 BRIGHT TIN OVER .000030 NICKEL.
7. POINT OF MEASUREMENT FOR PLATING THICKNESS.
8. .000015 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
9. .000030 GOLD ON CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
10. OBSOLETE PART NUMBER.



1	102104-6	102100-9/10
2	102104-5	102100-8/10
3	102104-4	102100-6
4	102104-3	102100-5
5	102104-2	102100-2
6	102104-1	102100-1
FINISH	LOOSE PIECE P/N	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .005$ ANGLES $\pm$	CONTRACT NO		 TE Connectivity		
	DR <i>AC Bedrin</i> 4/12/78				
	MATERIAL PHOS. BRONZE	CHK <i>Bedrin</i> 4-27-78		NAME CONTACT, MOD I, RECEPTACLE, CRIMP SNAP-IN, HIGH PRESSURE, #18 - #22AWG, SIDE FEED	
		APPD <i>Bedrin</i> 4/28/78 APPD <i>Bedrin</i> 5/1/78			
FINISH SEE TABLE	DSGN APPD		SIZE CODE IDENT NO DRAWING NO		
	OTHER APPD		C 00779 102100		
			SCALE SHEET		

CUSTOMER DRAWING