




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	ECR-25-239014	28APR2025	ABS	PS

12	OBSOLETE		2	2.59	1.295	1-103653-1	12	6-103946-1
	OBSOLETE		2	2.39	1.195	1-103653-0	1 1	6-103946-0
			2	2.19	1.095	103653-9	10	5-103946-9
			2	1.99	.995	103653-8	9	5-103946-8
			2	1.79	.895	103653-7	8	5-103946-7
			3	2.39	.795	103653-6	7	5-103946-6
			2	1.39	.695	103653-5	6	5-103946-5
			4	2.38	.595	103653-4	5	5-103946-4
			4	1.98	.495	103653-3	4	5-103946-3
			5	1.98	.395	103653-2	3	5-103946-2
			8	2.36	.295	103653-1	2	5-103946-1
12	OBSOLETE		8	2.36	.295	103653-1	2	1-103946-2
	OBSOLETE		2	2.59	1.295	1-103653-1	12	1-103946-1
	OBSOLETE		2	2.39	1.195	1-103653-0	1 1	1-103946-0
	SUPERSEDED BY 5-103946-9		2	2.19	1.095	103653-9	10	103946-9
	SUPERSEDED BY 5-103946-8		2	1.99	.995	103653-8	9	103946-8
	SUPERSEDED BY 5-103946-7		2	1.79	.895	103653-7	8	103946-7
			3	2.39	.795	103653-6	7	103946-6
			2	1.39	.695	103653-5	6	103946-5
			4	2.38	.595	103653-4	5	103946-4
			4	1.98	.495	103653-3	4	103946-3
			5	1.98	.395	103653-2	3	103946-2
			8	2.36	.295	103653-1	2	103946-1
		PLATING		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP

- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- FOR INDIVIDUAL ASSEMBLIES SEE PART NUMBER 103893
- ASSEMBLIES ARE JOINED BY THE CARRIER STRIP. ORDER QUANTITY REFLECTS TOTAL NUMBER OF INDIVIDUAL ASSEMBLIES REQUIRED. SEE TABLE FOR NUMBER OF ASSEMBLIES PER STRIP.
- MATERIAL- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK, PINS: PHOS. BRONZE
- FINISH- PINS: .000030 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, OVER .000050 NICKEL.
- FINISH- PINS: .000030 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.
- PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- FINISH- PINS: .000030 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, OVER .000050 NICKEL.

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R BROWN 26JUL00		 TE Connectivity				
			CHK K WRIGHT 26JUL00						
			APVD K WRIGHT 26JUL00						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, W/ LATCH WINDOWS, FOR NO 22-NO 26 AWG WIRE SIZE, STRIP FORM			
		0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-25034					
		APPLICATION SPEC 114-25026							
MATERIAL 		FINISH SEE TABLE		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C-103946	RESTRICTED TO -
CUSTOMER DRAWING						SCALE 4:1	SHEET 1 of 1	REV K3	