

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	12	ECN-25-356402	27OCT2025	GSK	AK


NOTES: —

1. CHARACTERS: —
- 0–9, A–Z, +, –, /,~, ≡
- 0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
- HEIGHT 1.8 – 2.0 mm
- TOLERANCE (AXIAL) ±0.75
- (ROTATIONAL) ±5°


CHEVRON CUT MARKERS: —

CHARACTERS TO BE CENTRALLY DISPOSED ON MARKER FACE AND IN THE ATTITUDE SHOWN RELATIVE TO CHEVRON.


2. MARKER LENGTHS (DIMENSION 'A'):
- WITH SINGLE MARK 3.70 – 4.50
- WITH DOUBLE MARK 5.75 – 6.25



CHEVRON CUT



STRAIGHT CUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V	 TE Connectivity			
		CHK 11FEB2020 ALAN KEAN				
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± 0.2 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	APVD 11FEB2020 ALAN KEAN	NAME MARKER Z TYPE SIZE 7 STRAIGHT / CHEVRON CUT			
		PRODUCT SPEC —				
MATERIAL PVC		APPLICATION SPEC —	SIZE A3	CAGE CODE A00YMC	DRAWING NO C-1601A0002	RESTRICTED TO —
FINISH —		WEIGHT 2.05–1.85g/250mm	CUSTOMER DRAWING			
		SCALE 10:1		SHEET 1 OF 1	REV 12	