






P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECO-11-005294	02APR11	RK	HMR
	D2	REVISED PER ECR-21-101087	05MAY2021	PJ	VS
	D3	REVISED PER ECN-35-360107	18DEC2025	WLS	JP

NOTES:

- FOR ADDITIONAL INFORMATION SEE DRAWING 163300.
- THIS TERMINAL IS SUPPLIED IN INDIVIDUAL FORM, NOT AS A CONTINUOUS STRIP.
- WIRE RANGE: 0.5-1.0 mm2.
- INSULATION RANGE: .070-.130 in. DIA (1.8-3.3 mm DIA).



OBSOLETE

PRE-TIN	Ph BRONZE	163304-4
NONE	Ph BRONZE	163304-3
PRE-TIN	BRASS	163304-2
PLATING	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. KESSLER	 TE Connectivity		
		CHK P. BEIJNON			
		APVD			
		PRODUCT SPEC 108-1000			
		APPLICATION SPEC 114-1012	NAME SOCKET MATE-N-LOK LOOSE PIECE		
		WEIGHT -	SIZE A3	CAGE CODE	RESTRICTED TO
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1	REV D3