





-	1	1	1	1	NEXTGEN MCON 1.2 LL CPA	PBT-GF30	RED	4													
1	1	1	1	1	6POS MCON 1.2 - SEAL	SILOPREN LSR	BLUE	3													
1	1	1	1	1	6POS, NEXTGEN MCON 1.2 - PROTEC. COVER	PA6-GF15	BLACK	2													
-	1	-	-	-	6POS NEXTGEN MCON 1.2 - RECEPTACLE HSG.- COD D	PBT-GF20	VIOLET	1													
-	-	1	-	-	6POS NEXTGEN MCON 1.2 - RECEPTACLE HSG.- COD C	PBT-GF20	BLUE	1													
-	-	-	1	-	6POS NEXTGEN MCON 1.2 - RECEPTACLE HSG.- COD B	PBT-GF20	BROWN	1													
1	-	-	-	1	6POS NEXTGEN MCON 1.2 - RECEPTACLE HSG.- COD A	PBT-GF20	BLACK	1													
1	-	6	4	-	13	-	12	-	11	-	1	DESCRIPTION	MATERIAL	COLOUR	ITEM NO						
C	C	C	C	C	C	C	REVISION														
QTY REQD PER ASSY					PARTS LIST																

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140@CENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY. Freimaßtoleranzen nach DIN 16901-140@. Es gilt die Ausgabe 1982-11.		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: 16APR2024 CHK: SZÉKELY LEHEL APVD: NEMESZ SZILÁRD GÁSPÁR SZABOLCS	NAME: 6POS,NEXTGEN, MCON 1.2 LL REC SEALED
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: 108-94874	SIZE: A
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		APPLICATION SPEC: 114-94767	CAGE CODE: 00779
MATERIAL: SEE BOM		WEIGHT: -		CUSTOMER DRAWING	DRAWING NO: C=2378606
				SCALE: 3:1	SHEET: 1 OF 1
				REV: 2	