









SECTION A-A



ADAPTER PLATE - HVP-HD1000 2POS HEADER INTERFACE



REVISIONS				
P	LTN	DESCRIPTION	DATE	APPD
-	-	SEE SHEET 1	-	-



TABLE 4					
*-1		*-2		*-3	
CODE A	CODE B	CODE C	CODE D	CODE E	CODE F
*-4		*-5		*-6	
CODE G	CODE H	CODE J	CODE K	CODE L	CODE M

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
(mm)

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
±0.5
2 P.L.C. ±0.1
3 P.L.C. ±0.001
4 P.L.C. ±0.001
FINISH

REV

26AUG2021

CHK

26AUG2021

APPD

26AUG2021

PRODUCT SPEC

108-160341

APPLICATION SPEC

114-160181

WEIGHT

SEE TABLE

CUSTOMER DRAWING

DATE

26AUG2021

NAME

2PDS,PIN DIA 10.0 HDR ASSY,90DEG
HVP-HD1000

SIZE

A0

CASE CODE

00779

DRAWING NO

C=2394071

RESTRICTED TO

-

SCALE

2:1

SHEET

3

OF

4

REV

02

TE Connectivity

