

4


3

2

1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

3 STRIPES EQUALLY
SPACED FOR COLOR
CODE: SEE TABLE



AMP WIRE RANGE	5 LR7189 Certified
SEE TABLE STRANDED	WIRE SIZE PER TABLE STRANDED

- 1 STAMP AMP APPROX AS SHOWN
SEE TABLE BELOW.
- 2 WIRE INSULATION DIA: $\varnothing 0.965-2.794[\varnothing 0.038-.110]$ FOR 22 AWG
 $\varnothing 1.168-2.794[\varnothing 0.046-.110]$ FOR 20 AWG
 $\varnothing 1.422-2.794[\varnothing 0.056-.110]$ FOR 18 AWG
- 3 BODY MATERIAL THK: $0.787\pm 0.051[.031\pm .002]$.
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE.
- 5 CSA CERTIFIED
- 6 MATERIAL:
BODY & SLEEVE - COPPER PER ASTM B152
INSULATION - NYLON
- 7 FINISH:
BODY & SLEEVE - TIN PLATE $0.00254[.000100]$ MIN EXT THK PER ASTM B545
INSULATION COLOR - RED

5	M7928/1-37 CLASS 1	WHITE	18*	18	1000	LOOSE PIECE	2-328975-3
5	M7928/1-28 CLASS 1	RED	20*	20	1000	LOOSE PIECE	2-328975-2
5	M7928/1-19 CLASS 1	GREEN	22*	22	1000	LOOSE PIECE	2-328975-1
	MILITARY P/N AND CLASS	STRIPE COLOR	1STAMPING	WIRE SIZE	QUANTITY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 9/8/93		 TE Connectivity Ltd.						
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 V MAX		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[0.005] 4 PLC ± - ANGLES ± - FINISH	CHK RE HERSEY 9/8/93	APVD ML ELLIS 9/8/93	NAME TERMINAL, RING TONGUE, PIDG™, WIRE SIZE, 22, 20 & 18 AWG					
	TOOLING ASSISTANCE CENTER 1-800-722-1111		WIRE RANGE: CIRC MIL AREA 22 0.38mm² [754] 20 0.60mm² [1,186] 18 0.96mm² [1,900] STRANDED							PRODUCT SPEC —					
FOR APPLICATION TOOLING INFORMATION	1-800-526-5142				MATERIAL 			FINISH 		APPLICATION SPEC 114-2157		SIZE A3	CAGE CODE 00779	DRAWING NO C-328975	RESTRICTED TO —
										WEIGHT —					
										CUSTOMER DRAWING		SCALE NTS	SHEET 2 OF 2	REV R2	