


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R5	REVISED PER ECR-25-255998	12SEP2025	SA	DSC



AMP WIRE RANGE	RU FILE E13288	SR LR7189 Certified
8 AWG STRANDED	8 AWG STRANDED	8 AWG STRANDED

- 1 STAMP AMP 8* LOCATE APPROX AS SHOWN
- 2 TONGUE MATERIAL THK 1.02±0.08[.040±.003]
- 3 SEE TABLE FOR WIRE INSULATION DIA MAX
- 4 TAPE ITEMS ARE ON 30.48[1.200] CENTERS

9.14 [.360]	33.99 [1.338]	39.52 [1.556]	1 KIT = 50 PIECES	LOOSE PC	6-52263-0
9.91 [.390]	33.99 [1.338]	39.52 [1.556]	100	LOOSE PC	52263-5
8.38 [.330]	34.49 [1.358]	40.03 [1.576]	500	ON TAPE	52263-4
9.14 [.360]	33.99 [1.338]	39.52 [1.556]			52263-3
8.38 [.330]	34.49 [1.358]	40.03 [1.576]			52263-2
9.14 [.360]	33.99 [1.338]	39.52 [1.556]	100	LOOSE PC	52263-1
					52263
WIRE INSULATION DIA	"B"	"A"	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 6.64-10.54mm²[13,100-20,800] STRANDED
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-29-93	TE TE Connectivity		
		CHK R. HERSEY 9-29-93			
DIMENSIONS: mm [INCHES]		APVD B. BARE 9-29-93	NAME TERMINAL, RING TONGUE, PLASTI-GRIP, WIRE SIZE: 8 AWG		
		PRODUCT SPEC NOT AVAILABLE			
		APPLICATION SPEC 114-2161	SIZE A3	CAGE CODE 00779	DRAWING NO C-52263
MATERIAL COPPER PER ASTM B-152 PVC, COLOR: RED		FINISH TIN PLATE PER ASTM-B545	WEIGHT -	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV R5