

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2015

© COPYRIGHT 2012

BY TE CONNECTIVITY




ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER PCN E-21-000055	13JAN2021	CO	IG
A2		REVISED PER PCN E-20-017587	10MAR2021	CO	IG
B		REVISED PER PCN-24-219306	29AUG2024	CO	CB
C		REVISED PER PCN-25-233228	19DEC2024	RK	CB



7. PART MODIFICATION: THREADED ADAPTER

- 6 CONDUIT ADAPTER ACCEPTS EITHER TYPES:
A. CONDUIT ADAPTER CAP NUT (CN21) AND SEAL RING (SRN21)
B. BACKSHELL (M902-2243), COMPRESSION NUT (M902-2053), CABLE Ø.430-.570 [10.92-14.78]
C. BACKSHELL (M902-2244), COMPRESSION NUT (M902-2054), CABLE Ø.570-710 [14.78-18.03]

- 5 MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
CONDUIT ADAPTER: PA66 GF10 (GREEN, GRAY, BLUE)
GROMMET: SILICONE (ORANGE-RED)

- 4 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOLS

3. THIS PLUG MATES WITH HDP24-24-91SX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XXXX = MODIFICATION

- 2 CAVITY 5 IS WITH CONTACT SIZE 16 AND THE GROMMET IS SEALED.
1 CONTACTS 4 AND 5 ARE INTERNALLY CONNECTED (BUILT-IN BRIDGE).

NOTES:

TE INTERNAL PN	DEUTSCH PN
HDP26-24-91SE-L015	HDP26-24-91SE-L015

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12MAY2012 ALDO MALAGON	 TE Connectivity		
DIMENSIONS: INCHES[mm]		CHK 24MAY2012 BRICE BYFORD			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 23MAY2012 STEVE BEARD	NAME PLUG, COUPLING RING SIZE 24, -L015 HDP SERIES		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.015 [.038] 4 PLC ± ANGLES ±0°30'0"		PRODUCT SPEC 0425-021-0000	SIZE A3		
MATERIAL 5		APPLICATION SPEC 4	CAGE CODE 4AFU8		
FINISH N/A		WEIGHT	DRAWING NO HDP26-24-91SX-L015		
		Customer Drawing	RESTRICTED TO -		
			SCALE 2:1		
			SHEET 1 OF 1		
			REV C		