


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	ECR-17-007409	25MAY2017	DL	CW
	D	ECR-21-117384	12NOV2021	WQR	CW
	DI	ECR:ADD NEW TYPE	11OCT2023	RW	CW
	E	ECR-25-237972	16JUN2025	ABS	RB

- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 400 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 400V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

T2080122101-100	HQ-012-M	HQ-012 MALE INSERT WITH CONDUCTIVE SEAL RING HQ-012 公插, 带导电密封圈
T2080122101-000	HQ-012-M	HQ-012 MALE INSERT HQ-012 公插
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID LI 31MAR2015	TE Connectivity													
		CHK CHRIS WANG 31MAR2015														
		APVD XU XIANG 31MAR2015														
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HQ-012-M													
	0 PLC	±-	SIZE A3				CAGE CODE -		DRAWING NO C-T2080122101000		RESTRICTED TO					
	1 PLC	±-														
	2 PLC	±-														
	3 PLC	±-														
	4 PLC	±-														
ANGLES		±-														
MATERIAL		FINISH	WEIGHT				CUSTOMER DRAWING		SCALE		SHEET		OF		REV	
-		-	-						2:1		1		1		E	
-		-														

M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
M3螺丝, 推荐扭力矩为0.5Nm

M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
M3螺丝, 推荐扭力矩为0.5Nm

(17.45)

32.8

21

21

GROUNDING CONTACT TYPE: SCREW CONTACT
GROUNDING CONTACT FINISH: SILVER PLATED
WIRE RANGE: 2.5mm² (AWG14)
接地针类型: 螺丝压接
接地针表面处理: 镀银
接线范围: 2.5mm² (AWG14)