

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

04MAR2004

© COPYRIGHT 04MAR2004 BY -


ALL RIGHTS RESERVED.

The contents indicated by this drawing are disclosing the information which Tyco Electronics owns. It forbids copying and distributing without notice.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED ECO-20-009888	16JUL19	J. J	W. H

- 1; AS SHOWN





- 1 PLATED
ALL OVER; Ni 0.8 μm MIN
CONTACT POINT; Au 0.25 μm 0.5 μm
SOLDERING AREA; Au 0.05 μm MIN
2. CUT BURR; 0.05 MAX.
OTHER BURR; 0.03 MAX.
- 3 MATERIAL; COPPER ALLOY
- 4 FEATURES IDENTIFIED AS STATISTIACLLY TOLERANCED (ST)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OHASHI 29JAN2004	 TE Connectivity		
DIMENSIONS: mm		CHK T. KIMURA 06APR2004			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2		APVD K. IKEGAMI 06APR2004	NAME SHIELD FINGER 2411 ANTI OVER STRESS TYPE EMBOSS PACKING		
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±		PRODUCT SPEC 108-5967	SIZE A3		
MATERIAL 2		APPLICATION SPEC -	CAGE CODE -		
FINISH 1		WEIGHT 0.01g	DRAWING NO C-1746854		
		CUSTOMER DRAWING	RESTRICTED TO		
			SCALE 2:1		
			SHEET 1 OF 2		
			REV A3		

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





WITH PRODUCT CHARGE
5,000EA/REEL
NO EMPTY POCKETS
ARE PERMITTED

300MIN COVER TAPE
100mm MIN WITHOUT CHARGE

PEELING ANGLE
165°~180°
PEELING FORCE
0.1N~1.0N

→ DIRECTION OF TOP OF REEL



SECTION A-A

- 1; AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. OHASHI 29JAN2004	TE Connectivity		
DIMENSIONS: mm		CHK T. KIMURA 06APR2004			
		APVD K. IKEGAMI 06APR2004			
		PRODUCT SPEC 108-5967			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ± 0.2		APPLICATION SPEC -	NAME SHIELD FINGER 2411 ANTI OVER STRESS TYPE EMBOSS PACKING		
0 PLC ± 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±		WEIGHT 0.01g	SIZE A3	CAGE CODE -	DRAWING NO C-1746854
FINISH SEE NOTE Y		CUSTOMER DRAWING	SCALE 4:1	SHEET 2 OF 2	REV A3