

IE-FM6D2UE0300MSD0SD0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5 , 6 and 14
- consistently Cat. 6_A with **STEADYTEC®** technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

General ordering data

Version	Dragline cable, SC duplex IP 20, SC duplex IP 20, 62.5 µm, PUR, 300 m
Order No.	8989610000
Type	IE-FM6D2UE0300MSD0SD0X
GTIN (EAN)	4032248856084
Qty.	1 pc(s).
Available until	2012-12-31

IE-FM6D2UE0300MSD0SD0X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	300 m	Length (inches)	11,811.023 inch
Net weight	14,726 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-20 °C...60 °C		

General standards

Connector standard	IEC 61754-4
--------------------	-------------

Fibre-optic

Attenuation	2.7 dB/km at 850 nm, ≤ 0.5 dB/km at 1300 nm	Bandwidth	200 MHz*km at 850 nm, 500 MHz*km at 1300 nm
Fibre type	GOF, Multimode, OM1	Insertion loss	≤ 0.4 dB
Return loss (attenuation)	≥ 30 dB		

Cable structure

Cable layout	Break-out dragline	Core diameter	62.5 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	100,000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	77 mm		

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03
ECLASS 13.0	27-06-10-03	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

IE-FM6D2UE0300MSD0SD0X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****V0 material**

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SF 6/21 MC NE WS V0	Version
Order No.	1730560001	SlimFix, Conductor and cable markers, 5.8 - 7.8 mm, 21 x 8.4 mm,
GTIN (EAN)	4008190954611	white
Qty.	160 pc(s).	
Type	VT SF 5/21 MC NE WS V0	Version
Order No.	1689470001	SlimFix, Conductor and cable markers, 4.8 - 7.4 mm, 21 x 7.4 mm,
GTIN (EAN)	4008190872571	white
Qty.	160 pc(s).	