

## MULTIMETER 1037

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

### General ordering data

Version	Testing tools, Multimeter
Order No.	<a href="#">9423580000</a>
Type	MULTIMETER 1037
GTIN (EAN)	4032248406142
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2025-08-31

## MULTIMETER 1037

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Dimensions and weights

Depth	66 mm	Depth (inches)	2.598 inch
Height	44 mm	Height (inches)	1.732 inch
Width	214.5 mm	Width (inches)	8.445 inch
Net weight	880 g		

## Technical data

Description of article	Version	Multimeter + clamp-on meter
Digital multimeter		

## Measuring and testing devices

AC voltage measuring range	0.2 - 750 V	Battery type	9V block battery
DC voltage measuring range	0.2 - 1000 V	Display	digital
Frequency measurement	No	Frequency range, max.	500 Hz
Frequency range, min.	50 Hz	Measured capacitance value, max.	200 µF
Measured current value, max.	200 A	Measuring range category	CAT III
Opening width of current-measuring clamp-on attachment	23 mm	Resistance measuring range, max.	200 kΩ
Resistance measuring range, min.	0.2 Ω	Selection of measuring range	Manual
Test probe	Yes	Tested and approved according to	EN/IEC 61010-1
Working temperature, max.	50 °C	Working temperature, min.	0 °C

## Classifications

ETIM 6.0	EC000069	ETIM 7.0	EC000069
ETIM 8.0	EC000069	ETIM 9.0	EC000069
ETIM 10.0	EC000069	ECLASS 9.0	27-20-03-01
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-01
ECLASS 11.0	27-20-03-01	ECLASS 12.0	27-20-03-01
ECLASS 13.0	27-20-03-01	ECLASS 14.0	27-20-03-01
ECLASS 15.0	27-20-03-01		

## Approvals

RoHS	Conform
------	---------

## Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

## Downloads

User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**MULTIMETER 1037**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings****Example of use**

**MULTIMETER 1037**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergsstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Digital multimeters**

Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

**General ordering data**

Type	ZUB MULTI 1037	Version
Order No.	<a href="#">9205460000</a>	Multimeter
GTIN (EAN)	4032248738731	
Qty.	1 pc(s).	

**Accessories**

Accessories for testing and measuring equipment

**General ordering data**

Type	BLOCKBATTERIE 9V	Version
Order No.	<a href="#">9004810000</a>	Testing tools, Battery
GTIN (EAN)	4008190050665	
Qty.	1 pc(s).	