
© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H	REVISED PER ECR-26-282233	30JUN2026	GSK	MP



AMP
WIRE RANGE
6 AWG
STRANDED

1 BODY MATERIAL THK 1.143±0.051[.045±.002]

2 FOR ø7.975[ø.314] MAX WIRE INS.

△3 STAMP AMP 6* 23-30 APPROX AS SHOWN.

△4 MATERIAL:
BODY – COPPER PER ASTM B152
INSULATION – NYLON

△5 FINISH:
BODY – TIN PLATE .000100 [0.00254]
MIN EXT PER ASTM B545
INSULATION – BLUE

100	LOOSE PC	324048
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F]

VOLTAGE RATING: –

CIRCULAR MIL AREA: 10.5-16.8mm² [20,800-33,100] STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± –
2 PLC	± –
3 PLC	± 0.127[.005]
4 PLC	± –
ANGLES	± –

MATERIAL △4

FINISH △5

DWN	S.S. GOULDEN 6-18-93
CHK	R. HERSEY 6-18-93
APVD	B. BARE 6-18-93
PRODUCT SPEC	108-162357
APPLICATION SPEC	—
WEIGHT	

TE Connectivity

NAME: TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 6 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-324048	—

CUSTOMER DRAWING

SCALE	SHEET	REV
NTS	1 OF 1	H