





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M1	REVISED PER ECR-25-242347	26APR2025	AG	DH


- 1
- CONTINUOUS STRIP ON REELS.
- 2
- MATING TAB THK TO BE 0.51 ± 0.025 [.020±.001].
- 3
- WIRE SIZE IS [#22-#18] AWG.
- 4
- INSULATION RANGE IS 2.03-3.05 [.080-.120] DIA.



VIEW A-A
SCALE 8:1



SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

OBSOLETE	MATTE-TIN	63241-3
	0.002032 [.000080] MIN TIN	63241-2
	-	63241-1
	FINISH	PART NO.

F	3.56 [.140]	3.96 [.156]	F	1.78 [.070]	0.94 [.037]	[#22]
					1.02 [.040]	[#20]
					1.14 [.045]	[#18]
TYPE	WIDTH	STRIP LENGTH ±0.38 ±[.015]	TYPE	WIDTH	±.051±.002 HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 3/27/97	TE Connectivity			
		CHK MS FEHER 3/27/97				
	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME RECEPTACLE, FASTIN-FASTON, 2.79 [.110] SERIES			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -				
MATERIAL BRASS		FINISH SEE TABLE	APPLICATION SPEC 114-2065	SIZE A3	CAGE CODE 00779	DRAWING NO C-63241
CUSTOMER DRAWING			WEIGHT 0.000000	RESTRICTED TO -	SCALE 5:1	SHEET 1 OF 1
					REV M1	