





REVISIONS					
P	LTR	DESCRIPTION		DATE	APVD
	B2	PART STATUS CHANGE TO DISCONTINUANCE		08JUL2026	NS PS



796981-3 AS SHOWN



POLARIZATION KEY SLOT

1. MATERIALS AND FINISH:
HOUSING: PA 6-6, UL 94-V0, COLOR: SEE P/N TABLE.
CLAMP: BRASS, NICKEL PLATED.
DOUBLE SIDE CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. WIRE SIZE RANGE
SOLID WIRE: 12-30AWG
STRANDED WIRE: 12-30AWG
3. RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. FILE N° E60677.
4. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.

5. NOT CUMULATIVE TOLERANCE

OBSOLETE

GREEN	89.44	12	1-796981-2
GREEN	81.82	11	1-796981-1
GREEN	74.20	10	1-796981-0
GREEN	66.58	9	796981-9
GREEN	58.96	8	796981-8
GREEN	51.34	7	796981-7
GREEN	43.72	6	796981-6
BLACK	36.10	5	2-796981-5
GREEN	36.10	5	796981-5
GREEN	28.48	4	796981-4
GREEN	20.86	3	796981-3
GREEN	13.24	2	796981-2
COLOR	DIM L.	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI CHK D. BIEVENOUR APVD D. BIEVENOUR	28MAR2001 28MAR2001 28MAR2001	TE Connectivity		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±2	PRODUCT SPEC -	APPLICATION SPEC -	NAME TERMINAL BLOCK, PLUG 7.62mm PITCH		
MATERIAL	FINISH	WEIGHT -	CUSTOMER DRAWING	SIZE A2	CAGE CODE b0779	DRAWING NO C-796981
				RESTRICTED TO -	SCALE NTS	SHEET 1 OF 1
				REV B2		