


# Captive Screw Type 5 6-32 Thread



Create a part number:

| Length | Material | Finish |
|--------|----------|--------|
| FCXXXX | XX       | XX     |
| <hr/>  |          |        |

| Captive Screws - 6-32 Thread |            |          |  |
|------------------------------|------------|----------|--|
| ✓ FCXXXX                     | Length (L) | S.L. REF |  |
| FC0908                       | 7/16       | 3/32     |  |
| FC0909                       | 1/2        | 5/32     |  |
| FC0910                       | 9/16       | 7/32     |  |
| FC0911                       | 5/8        | 9/32     |  |
| FC0912                       | 11/16      | 11/32    |  |
| FC0913                       | 3/4        | 13/32    |  |
| FC0914                       | 13/16      | 15/32    |  |
| FC0915                       | 7/8        | 17/32    |  |
| FC0916                       | 15/16      | 19/32    |  |
| FC0917                       | 1          | 21/32    |  |
| FC0918                       | 1-1/16     | 23/32    |  |
| FC0919                       | 1-1/8      | 25/32    |  |
| FC0920                       | 1-3/16     | 27/32    |  |
| FC0921                       | 1-1/4      | 29/32    |  |
| FC0922                       | 1-5/16     | 31/32    |  |
| FC0923                       | 1-3/8      | 1-1/32   |  |
| FC0924                       | 1-7/16     | 1-3/32   |  |
| FC0925                       | 1-1/2      | 1-5/32   |  |

| Material             |                 |  |
|----------------------|-----------------|--|
| ✓ Material Code (XX) |                 |  |
| B                    | Brass           |  |
| S                    | Steel           |  |
| SS                   | Stainless Steel |  |

| ✓ Compatible Finish (XX) |                                       |  |
|--------------------------|---------------------------------------|--|
| B, S, SS                 | 0 - Plain                             |  |
| B, S                     | 5 - Nickel Plate (QQ-N-290)           |  |
| B, S                     | 12 - Zinc Clear (ASTM-B-633)          |  |
| B, S                     | 16 - Electro Tin (MIL-T-10727 TYPE 1) |  |
| SS                       | 20 - Passivation (MIL-F-14072D)       |  |
| B, S, SS                 | 26 - Black Oxide                      |  |
| B, S                     | 28 - Zinc Yellow (ASTM-B-633)         |  |

**Tolerances Unless otherwise Specified**  
 .xxx +/- .005  
 .xx +/- .010  
 Angular +/- 1 Degree  
 Linear +/- .005  
**Break all sharp edges**

Source Control Drawing:  
 To be produced by  
 Fascomp Electronic Hardware



This document is the property of Fascomp Inc. and shall not be reproduced, distributed, or used as a basis for manufacturing without written permission from Fascomp Inc.