


5/16 Round Off-Set Internal Thread Handles



Create a part number:

Part	Thread	Material	Finish
FCXXXX	XXX	XX	XX
_____ - _____ - _____ - _____			

✓	FCXXXX	Length (L) +/- .031	Leg Height (H) +/- .031
	FC8279	2	1-5/16
	FC8280	2-1/2	1-5/16
	FC8281	3	1-5/16
	FC8282	4	1-5/16
	FC8283	5	1-5/16
	FC8284	6	1-5/16
	FC8285	3	1-1/2
	FC8286	4	1-1/2
	FC8287	4-1/4	1-1/2
	FC8288	4-1/2	1-1/2
	FC8289	4-9/16	1-1/2
	FC8290	5	1-1/2
	FC8291	5-1/2	1-1/2
	FC8392	6	1-1/2
	FC8293	3	1-3/4
	FC8294	4	1-3/4
	FC8295	4-1/4	1-3/4
	FC8296	4-1/2	1-3/4
	FC8297	4-9/16	1-3/4
	FC9298	5	1-3/4
	FC8299	5-1/2	1-3/4
	FC8300	6	1-3/4

Thread (A)			
Short lengths, 'A' tapped to maximum depth			
✓	Code (XXX)	Thread	(A)
	832	8-32	5/16 - 7/16
	1032	10-32	5/16 - 1/2

Material		
✓	Material Code (XX)	
	A	Aluminum
	B	Brass
	SS	Stainless Steel

✓	Compatible Finish	
	A, B, S, SS	0 - Plain
	B, S	5 - Nickel Plate (QQ-N-290)
	A	6 - Iridite #14 Gold (MIL-C-5541E)
	A	7 - Iridite Clear (MIL-C-5541E)
	A	9 - Alodine 1200
	B, S	12 - Zinc Clear (ASTM-B-633)
	B, S	16 - Electro Tin (MIL-T-10727 TYPE 1)
	SS	20 - Passivation (MIL-F-14072D)
	A	22 - Clear Anodize (MIL-A-8625-TYPE2) (Sulphuric) Hot Water Seal (Clear)
	A	24 - Black Anodize (MIL-A-8625)
	B, S, SS	26 - Black Oxide
	B, S	28 - Zinc Yellow (ASTM-B-633)

Source Control Drawing:
To be produced by
Fascomp Electronic Hardware

Tolerances
Unless otherwise Specified
.xxx +/- .005
.xx +/- .010
Angular +/- 1 Degree
Linear +/- .005
Break all sharp edges



This document is the property of
Fascomp Inc. and shall not be
reproduced, distributed or used as a
basis for manufacturing without
written permission from Fascomp
Inc.