

RES-D

~16° diffused spot beam optimized for LUXEON Rebel. Assembly with white holder.

SPECIFICATION:

Dimensions	21.6 x 21.6
Height	12.9 mm
Fastening	tape
ROHS compliant	yes ⓘ



MATERIALS:


Component	Type	Material	Colour	Finish	Length (mm)
ROSE-TAPE	Tape	Acryl tape	grey		
ROSE-HLD-RE-WHT	Holder	PC	white		
» Box size: 480 x 280 x 300 mm					
ROSE-B-B-D	Single lens	PC	clear		
» Box size: 480 x 280 x 300 mm					

ORDERING INFORMATION:

Quantities for one set:

Single lens	1
Assembly	1

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F10284_ROSE-B-B-D	1980	180	180	8.0
CA10554_ROSE-HLD-RE-WHT	3240	180	180	7.2




See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED LUXEON Rebel
FWHM / FWTM 13.0° / 26.0°
Efficiency 84 %
Peak intensity 9.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED LUXEON Rebel ES
FWHM / FWTM 13.0° / 27.0°
Efficiency 86 %
Peak intensity 10 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED CSP 2323 (BXCP)
FWHM / FWTM 14.0° / 28.0°
Efficiency 87 %
Peak intensity 10.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files




LED XQ-E HD
FWHM / FWTM 8.0° / 14.0°
Efficiency 93 %
Peak intensity 45.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED XQ-E HD Blue
FWHM / FWTM 8.0° / 14.0°
Efficiency 94 %
Peak intensity 43.1 cd/lm
LEDs/each optic 1
Light colour/type Blue
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XQ-E HD Green
FWHM / FWTM 8.0° / 14.0°
Efficiency 94 %
Peak intensity 42.3 cd/lm
LEDs/each optic 1
Light colour/type Green
Required components:



Light distribution files




LED XQ-E HD Red
FWHM / FWTM 8.0° / 14.0°
Efficiency 92 %
Peak intensity 38.3 cd/lm
LEDs/each optic 1
Light colour/type Red
Required components:



Light distribution files



LED XQ-E HD WW
FWHM / FWTM 8.0° / 14.0°
Efficiency 92 %
Peak intensity 43.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED	LUXEON Rebel Plus
FWHM / FWTM	12.0° / 23.0°
Efficiency	88 %
Peak intensity	15.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)