

## The RF Line NPN Silicon Power Transistor


### 250W, 30MHz, 50V

Rev. V2

Designed primarily for high-voltage applications as a high-power linear amplifiers from 2.0 to 30 MHz. Ideal for marine and base station equipment.

- Specified 50 V, 30 MHz characteristics  
Output power = 250 W  
Minimum gain = 12 dB  
Efficiency = 45%
- Intermodulation distortion @ 250 W (PEP) —  
IMD = -30 dB (max)
- 100% tested for load mismatch at all phase angles with 3:1 VSWR

#### Product Image



#### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	$V_{CEO}$	50	Vdc
Collector-Base Voltage	$V_{CBO}$	100	Vdc
Emitter-Base Voltage	$V_{EBO}$	4.0	Vdc
Collector Current — Continuous	$I_C$	16	Adc
Withstand Current — 10 s	—	20	Adc
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ (1) Derate above $25^\circ\text{C}$	$P_D$	290 1.67	Watts $\text{W}/^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	-65 to +150	°C

#### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.6	°C/W

#### ELECTRICAL CHARACTERISTICS ( $T_C = 25^\circ\text{C}$ unless otherwise noted.)

Characteristic	Symbol	Min	Typ	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	0.6			°C/W

#### OFF CHARACTERISTICS

Collector-Emitter Breakdown Voltage ( $I_C = 200 \text{ mA}\text{dc}$ , $I_B = 0$ )	$V_{(BR)CEO}$	50	—	—	Vdc
Collector-Emitter Breakdown Voltage ( $I_C = 100 \text{ mA}\text{dc}$ , $V_{BE} = 0$ )	$V_{(BR)CES}$	100	—	—	Vdc
Collector-Base Breakdown Voltage ( $I_C = 100 \text{ mA}\text{dc}$ , $I_E = 0$ )	$V_{(BR)CBO}$	100	—	—	Vdc
Emitter-Base Breakdown Voltage ( $I_E = 10 \text{ mA}\text{dc}$ , $I_C = 0$ )	$V_{(BR)EBO}$	4.0	—	—	Vdc

NOTE:

1.  $P_D$  is a measurement reflecting short term maximum condition. See SOAR curve for operating conditions.

(continued)

The RF Line NPN Silicon Power Transistor  
250W, 30MHz, 50V

Rev. V2

ELECTRICAL CHARACTERISTICS — continued ( $T_C = 25^\circ\text{C}$  unless otherwise noted.)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

## ON CHARACTERISTICS

DC Current Gain ( $I_C = 5.0 \text{ Adc}$ , $V_{CE} = 10 \text{ Vdc}$ )	$h_{FE}$	10	30	—	—
--	----------	----	----	---	---

## DYNAMIC CHARACTERISTICS

Output Capacitance ( $V_{CB} = 50 \text{ Vdc}$ , $I_E = 0$ , $f = 1.0 \text{ MHz}$ )	$C_{ob}$	—	350	450	pF
---	----------	---	-----	-----	----

## FUNCTIONAL TESTS


Common-Emitter Amplifier Power Gain ( $V_{CC} = 50 \text{ Vdc}$ , $P_{out} = 250 \text{ W CW}$ , $f = 30 \text{ MHz}$ , $I_{CQ} = 250 \text{ mA}$ )	$G_{PE}$	12	14	—	dB
Collector Efficiency ( $V_{CC} = 50 \text{ Vdc}$ , $P_{out} = 250 \text{ W}$ , $f = 30 \text{ MHz}$ , $I_{CQ} = 250 \text{ mA}$ )	$\eta$	—	45	—	% (PEP) % (CW)
Intermodulation Distortion (2) ( $V_{CE} = 50 \text{ Vdc}$ , $P_{out} = 250 \text{ W (PEP)}$ , $I_{CQ} = 250 \text{ mA}$ , $f = 30 \text{ MHz}$ )	IMD	—	-33	-30	dB
Electrical Ruggedness ( $V_{CC} = 50 \text{ Vdc}$ , $P_{out} = 250 \text{ W CW}$ , $f = 30 \text{ MHz}$ , VSWR 3:1 at all Phase Angles)	$\Psi$	No Degradation in Output Power			

## NOTE:

2. To Mil-Std-1311 Version A, Test Method 2204, Two Tone, Reference each Tone.

The RF Line NPN Silicon Power Transistor  
250W, 30MHz, 50V

Rev. V2



C1, C2, C5, C7 — 170–780 pF, Arco 469

C3, C8, C9 — 0.1  $\mu$ F, 100 V ErieC4 — 500  $\mu$ F @ 6.0 V

C6 — 360 pF, 3 x 120 pF 3.0 kV in parallel

C10 — 10  $\mu$ F, 100 VR1 — 10  $\Omega$ , 10 WattR2 — 10  $\Omega$ , 1.0 Watt

CR1 — 1N4997 or equivalent

L1 — 3 Turns, #16 Wire, 0.4" I.D., 0.3" Long

L2 — 0.8  $\mu$ H, Ohmite Z-235 or equivalent

L3 — 12 Turns, #16 Enamelled Wire Closewound 0.25" I.D.

L4 — 4 Turns, 1/8" Copper Tubing, 0.6" I.D., 1.0" Long

L5, L6 — 2.0  $\mu$ H, Fair-Rite 2643021801 Ferrite bead each or equivalent

Figure 1. 30 MHz Test Circuit Schematic

## The RF Line NPN Silicon Power Transistor 250W, 30MHz, 50V

Rev. V2




Figure 2. Output Power versus Input Power




Figure 3. Output Power versus Supply Voltage




Figure 4. Power Gain versus Frequency






Figure 5. RF SOAR (Class AB)  
 $P_{out}$  versus Output VSWR

## The RF Line NPN Silicon Power Transistor 250W, 30MHz, 50V

Rev. V2

Figure 6.  $f_T$  versus Collector CurrentFigure 7. IMD versus  $P_{out}$

The RF Line NPN Silicon Power Transistor  
250W, 30MHz, 50V

Rev. V2




Figure 8. Output Resistance and Capacitance  
versus Frequency





Figure 9. Series Equivalent Impedance

The RF Line NPN Silicon Power Transistor  
250W, 30MHz, 50V

Rev. V2



Unless otherwise noted, tolerances are inches  $\pm .005''$  [millimeters  $\pm 0.13\text{mm}$ ]

## The RF Line NPN Silicon Power Transistor 250W, 30MHz, 50V

Rev. V2

M/A-COM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with M/A-COM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.