



# BIAS 6 Watt LED Drivers

## Universal Input/Output with AOVC™

BPWXLD 6-21U-035 (350mA, 0-10 dimmable)  
BPWXLD 6-9U-070 (700mA, 0-10 dimmable)



### Benefits

- Bias Adaptive Output Voltage Control, AOVC™ technology (patent pending) provides the broadest range of applications with the fewest driver SKUs
- Highly reliable, rugged construction for indoor or outdoor applications
- True 0-10 volt dimming with 1000:1 range, IEC 60929 compatible
- 1% current regulation and no flicker
- Color coded flying leads for simple assembly and installation
- AC line or DC load switching without overshoot on startup

### Operating Specifications

(@120VAC / 60 Hz / 25°C unless otherwise specified)




### Features

- Universal Input (100-308 VAC, 50/60Hz)
- Universal Output with AOVC™ (3-21VDC@350mA), (3-9VDC@700mA)
- Ingress protection to IP67
- -40 to +85°C ambient, 90°C maximum case temperature
- Flying Leads for AC and LED connections
- 3000 VAC Isolation
- EN 55022, Class B; FCC Part 15, Class B
- Overcurrent, short circuit (shorted string), open circuit (string break) and overload protected


Environmental	
Operating Temperature	-40 to 85° C
Case Temperature, maximum	90° C
Storage Temperature	-40 to 105° C
Ingress Protection	IP67
Mechanical	
Package Size (L x W x H)	1.9 x 1.74 x 0.94 inches
Lead Length	11", 18AWG 600V class
Safety and Standards	
Safety Compliance	UL: 60950-1, 2nd Ed./CSAC22.2 60950-1-07 2nd Ed.
EMI Emissions	EN 55022, Class B, FCC Part 15, Class B

Electrical	
Input Voltage Range	100-308 VAC (50/60Hz)
Output Power (Pmax)	6 W nom (50/60Hz)
String Voltage (Minimum)	3.0 VDC
Efficiency	75% nom.
Temperature Regulation Io (Peak)	+/- 2%, Po < Pmax
Isolation	3000 VAC
Earth Leakage @ 120 VAC	< 10 uA
Short Circuit Protection	Continuous, Pin ≤ 0.7 w @ 120 VAC
Reliability @ 25° C, MIL HDBK-217F	> 500 Khr MTBF
0-10 VDC Dimming	Per IEC 60929, Annex E
Line Regulation, Io (Peak)	+/- 1%, Po < Pmax
AC Input Connections	Line BLK, Neutral WHT
DC Output Connections	Pos(+) RED, Neg (-) BLU
Dimming (0-10 VDC) Connections	Adjust PUR/Com GRY


Model Number	String Voltage	Output Current	Dimming
BPWXLD 6-9U-070	3-9 VDC	0 - 700 mA	0 - 10 VDC, Vd
BPWXLD 6-21U-035	3-21 VDC	0 - 350 mA	0 - 10 VDC, Vd



AC Side View



Top View



Powered by  
**CITA**  
technologies

5 Year Limited Warranty - see Bias Power published warranty for specifics

[www.citapower.com](http://www.citapower.com)

BPWXLD 6 Series Data Sheet, Page 1 of 2

Revision 1d

Specifications subject to change