

DAISY

Solutions for premium class indoor lighting. Part of LEDiL's Dark Light concept with UGR <19. Optimized for 2835 and compatible with up to 5630 size mid-power LED packages.

DAISY is a perfect solution for premium class indoor lighting with a seamless glare eliminating shade and highly efficient lenses. Available in 28X1, 4X1, 7X1, 8X1, 2X2 and MINI form factors in black or white with gloss or matt finish. Can be adapted to many types of recessed, surface mounted or pendant luminaire designs.


DAISY-7X1

280 x 40 mm linear solution with 7X1 shade in gloss and matt black, white and metal



PRODUCTS:


DAISY-7X1-BW



Dimensions: 40.0 mm x 259.0 mm
Height: 40.00 mm

~80° batwing beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.


DAISY-7X1-W



Dimensions: 279.5 mm x 39.6 mm
Height: 20.30 mm

~50° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W-D



Dimensions: 279.5 mm x 39.6 mm
Height: 20.30 mm


~50° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.



**PRODUCT FAMILY
DATASHEET
DAISY-7X1**

PRODUCTS:

DAISY-7X1-O-D




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~25 + 70° oval beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-M




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~35° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-FT-D




Dimensions: 40.0 mm x 259.0 mm

Height: 20.30 mm

Forward throwing beam for freestanding office luminaires. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~80° wide beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-WW-D




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~80° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-O




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~25 + 70° oval beam. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

PRODUCTS:

DAISY-7X1-WAS




Dimensions: 279.4 mm x 40.0 mm

Height: 27.00 mm

Asymmetric beam for wall-washing

DAISY-7X1-M-D




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~35° wide beam. Variant with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

~50° wide beam with tighter cutoff. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-W2-D




Dimensions: mm x mm

Height: mm

~50° wide beam with diffused lenses. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-ZT25




Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

Asymmetric beam for aisle lighting. Clear version for high contrast lighting. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

DAISY-7X1-ZT25-D



Dimensions: 279.5 mm x 39.6 mm

Height: 20.30 mm

Asymmetric beam for aisle lighting. Diffused version for perfect colour mixing. Choose SHD with no lips or SHD2 with narrow lips and square openings. SHD3 with narrow lips and round openings.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Poznan, Poland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)