



## SPECIFICATIONS

FLIR Si2-Pro	
Acoustic measurement	124 low-noise MEMS microphones, real-time sound visualization
Detection threshold	20 kHz: -15 dB SPL 35 kHz: 4 dB SPL 50 kHz: 10 dB SPL 80 kHz: 36 dB SPL 100 kHz: 51 dB SPL
Bandwidth	2–130 kHz
Directional resolution	From 1° up to 0.125°
Operating distance	From 0.3 m (1.0 ft) up to 200 m (656 ft)
Severity assessment	Automatic AI-based severity assessment including recommended actions onboard camera
Leak localization and detection	Automatic leak recognition including estimated leak size and annual cost
Leak rate detection threshold	0.0032 l/min from 2.5 m, 0.0044 l/min from 6 m
Gases detected	Detects all gases provided they are under sufficient pressure. Quantifies leak rate costs for compressed air, ammonia, argon, carbon dioxide, helium, hydrogen, methane, natural gas, and nitrogen.
Other acoustic analysis modes	Mechanical fault detection
Imaging & Optical	
Digital camera	12 MP color
Camera field of view	75° diagonal
Video frame rate	Camera: 60 fps; Acoustic image: 30 fps; Screen: 70 fps
Zoom	8x Digital zoom
Video image resolution	1280 × 720

## Key Features

- Mechanical fault detection for early identification of bearing problems, preventing costly downtime
- Quantify leak rate and cost of industrial gas and compressed air leaks, to prioritize repair and calculate savings
- On-camera and in-software severity assessment and type classification of partial discharge (PD) issues
- Automatic frequency tuning, 8x zoom, 12 MP digital camera,
- IP54 rating, and a QR code reader
- Fleet management functionality for efficient tool usage and maintenance across large-scale operations

## Main Applications

- Ideal for routine inspections and preventative maintenance in various industrial settings
- Ensures adherence to safety standards by identifying potential hazards in bearings and gas systems
- Aids in managing and reducing operational costs through early leak detection and analysis
- Mechanical fault mode to detect faulty bearings to help plan repairs and avoid downtime

## User Interface

Display	Size: 5 in. 1280 × 720 Resistive touch screen, TFT LCD, MIPI DSI
Integrated flashlight	LEDs, two modes: ON / OFF

## Analysis and Reporting

Online	FLIR Acoustic Camera Viewer (cloud service) <a href="https://acousticviewer.flir.com">https://acousticviewer.flir.com</a>
Offline	FLIR Thermal Studio (desktop software)

## Communication and Data Storage

Data transfer	Wi-Fi 2.4 GHz and 5 GHz IEEE 802.11.b/g/n/ac wireless LAN, USB memory stick, Acoustic USB Adapter Cable
Camera software update	Automatic Over The Air (OTA) wireless update or via USB connection
Still image format	.nlz and .jpg
Video recording & format	Up to 5 minutes (.nlz format)
Storage, internal	128 GB (SD card)
Storage, external	USB 8 GB, Cloud storage capacity is unlimited
Image annotations	Image tags, comments, and GPS coordinates

## Power Supply

Camera power input	Nominal input voltage: 12 V DC Max input: 17 V DC , 3.3 A (limited)
--------------------	--

Battery	Li-Ion rechargeable battery pack (RRC 2054):14.4 V DC, 3.45 Ah, 49.68 Wh Usage: Up to 2.5 h Charge time: approx. 2 h Max output: 16.8 V DC, 5 A
---------	--

Specifications subject to change. For the most up-to-date specifications, please visit [flir.com](http://flir.com).

**SPECIFICATIONS, CONT.**

Battery charger	Input: 19–26 V DC, 2.8 A Max output: 17.4 V DC, 4.8 A
<b>Environmental Data</b>	
Operating temperature range	-10°C to 50°C (14°F to 122°F)
Storage temperature range	-20°C to 50°C max -20°C to 25°C recommended (determined by the battery)
Relative humidity	0–90% recommended
EMC	CFR47 FCC Part 15 Subpart B
Radio	CFR47 FCC Part 15 Subpart C/E, ETSI EN 301 489-1/-17, ETSI EN 300 328, ETSI EN 301 893
Ingress protection	IP54
Safety	IEC 62368-1
Declaration of conformity	See: <a href="https://support.flir.com/resources/DoC">https://support.flir.com/resources/DoC</a>
<b>Physical Data</b>	
Camera size	184 x 276 x 167 mm (7.2 x 10.8 x 6.5 in)
Camera weight	~ 1.2 kg
Battery size	85 x 77 mm (RRC2504)
Battery weight	~ 0.25 kg
Total weight	~ 1.45 kg (camera + battery)

<b>Warranty and Service</b>	
Warranty	<a href="http://www.flir.com/warranty/">http://www.flir.com/warranty/</a>
<b>Shipping Information</b>	
Packaging, type	Cardboard box
Packaging, contents	Camera Battery (2 ea) Battery charger Power cable (4 ea) Neck strap Hard transport case License card: FLIR Si-series Plugin for FLIR Thermal Studio, Perpetual license Printed documentation USB memory stick
Packaging, weight	6 kg (13 lb)
Packaging, size	365 x 190 x 490 mm (14.4 x 7.5 x 19.3 in)
EAN-13	7332558035702
UPC-12	845188033644
P/N	T912603

Specifications subject to change. For the most up-to-date specifications, please visit [flir.com](http://flir.com).

