



Datasheet

LL01CR-ZE××L02-U×-T

Available Distribution




LED



Recommend Applications



General Information




- Lens Material PC
- Lens Color Transparent
- Operating Temperature -40°C~+110°C
- Light Transmission Rate 400nm~900nm > 90%
- ⚠️ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠️ Never use any commercial cleaning solvents on lenses, like alcohol.
- 🧤 Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Dimensions

Part Number	Diameter	Height
LL01CR-ZE××L02	Ø35	20.4
LL01CR-ZE××L02-U×-T	Ø37.1	20.7

*All dimensions are in millimeters.

Packaging Details (SPQ)



Accessories




- Available with Holder LL01CROP45H×
- Available with Tape LL01A00XTPX

Mechanical Specification

*All dimensions are in millimeters.

Lens Dimension

LL01CR-ZE×L02





Assembly Instruction

Part No LL01CR-ZE×L02

Fixing Method



Luminaire Accessories



Lift lens and have its bottom aligned with the top of LED's light emitting surface.


Assembly Instruction

Part No LL01CR-ZE×L02

Fixing Method




Luminaire Accessories



Lift lens and have its bottom aligned with the top of LED's light emitting surface.

Holder Dimension

LL01CROP45H×



Assembly Instruction

Part No LL01CR-ZE×L02-U×-T
Holder LL01CROP45H×
Tape LL01A00XTPX



Fixing Method




Tape




Luminaire Accessories




Photometric Distribution



Photometric Distribution



Details by LED

Part No	Holder	Tape	LED Package Size	LED
LL01CR-ZE××L02	-	-	LES Ø4.6~8.9 1314 / 3535 5050 / 7070	 bridgelux V6  CITIZEN CLL010  CITIZEN CLU710  CREE CXB1512  CREE MHB-A  CREE XHP35-HD  CREE XHP35-HI  CREE XHP50 GEN2  CREE XHP70B  CREE XML2  CREE XP-G3  LUMILEDS L2C5-1202E0600  LUMINUS CXM-6  LUMINUS CXM-7  LUMILEDS LUXEON 5050  LUMILEDS LUXEON M  LUMILEDS LUXEON S  NICHIA NS9x383  OSRAM DURIS S8
LL01CR-ZE××L02-U×-T	 LL01CROP45H×  LL01A00XTPX		5050 / 7070 / 9090	 CREE JR5050  CREE MK-R  CREE MK-R2  CREE MTG  CREE MTG2

LED	Part No	FWHM	cd / lm	IES
	LL01CR-ZE20L02	20°	4.3	
	LL01CR-ZE30L02	22°	4.4	
	LL01CR-ZE45L02	39°	1.3	
	LL01CR-ZE20L02	21°	4.1	
	LL01CR-ZE30L02	22°	4.2	
	LL01CR-ZE45L02	37°	1.5	
	LL01CR-ZE20L02	24°	2.9	
	LL01CR-ZE30L02	27°	2.6	
	LL01CR-ZE45L02	45°	1.1	
	LL01CR-ZE20L02	24°	2.6	
	LL01CR-ZE30L02	28°	2.5	
	LL01CR-ZE45L02	45°	1.1	
	LL01CR-ZE20L02-U2-T	19°	5.7	
	LL01CR-ZE30L02-U2-T	19°	6.0	
	LL01CR-ZE45L02-U2-T	-	-	-
	LL01CR-ZE20L02	21°	4.5	
	LL01CR-ZE30L02	20°	5.5	
	LL01CR-ZE45L02	36°	1.6	
	LL01CR-ZE20L02-U2-T	19°	5.0	
	LL01CR-ZE30L02-U2-T	22°	4.6	
	LL01CR-ZE45L02-U2-T	45°	1.2	
	LL01CR-ZE20L02-U2-T	20°	4.7	
	LL01CR-ZE30L02-U2-T	23°	4.3	
	LL01CR-ZE45L02-U2-T	41°	1.3	
	LL01CR-ZE20L02-U2-T	22°	4.0	
	LL01CR-ZE30L02-U2-T	29°	3.0	
	LL01CR-ZE45L02-U2-T	49°	1.0	
	LL01CR-ZE20L02-U2-T	22°	3.7	
	LL01CR-ZE30L02-U2-T	26°	3.4	
	LL01CR-ZE45L02-U2-T	-	-	-
	LL01CR-ZE20L02	18°	6.2	
	LL01CR-ZE30L02	17°	6.8	
	LL01CR-ZE45L02	38°	1.5	
	LL01CR-ZE20L02	18°	6.4	
	LL01CR-ZE30L02	16°	7.8	
	LL01CR-ZE45L02	33°	1.7	
	LL01CR-ZE20L02	20°	4.6	
	LL01CR-ZE30L02	24°	3.8	
	LL01CR-ZE45L02	41°	1.3	

LED	Part No	FWHM	cd / lm	IES
	LL01CR-ZE20L02	23°	3.7	
	LL01CR-ZE30L02	27°	3.2	
	LL01CR-ZE45L02	47°	1.0	
	LL01CR-ZE20L02	20°	2.3	
	LL01CR-ZE30L02	-	-	-
	LL01CR-ZE45L02	-	-	-
	LL01CR-ZE20L02	18°	5.9	
	LL01CR-ZE30L02	17°	7.3	
	LL01CR-ZE45L02	-	-	-
	LL01CR-ZE20L02	22°	3.7	
	LL01CR-ZE30L02	23°	3.6	
	LL01CR-ZE45L02	40°	1.4	
	LL01CR-ZE20L02	21°	4.2	
	LL01CR-ZE30L02	23°	4.3	
	LL01CR-ZE45L02	39°	1.4	
	LL01CR-ZE20L02	24°	3.0	
	LL01CR-ZE30L02	25°	2.6	
	LL01CR-ZE45L02	25°	2.5	
	LL01CR-ZE20L02	20°	5.1	
	LL01CR-ZE30L02	19°	5.9	
	LL01CR-ZE45L02	33°	1.6	
	LL01CR-ZE20L02	20°	4.7	
	LL01CR-ZE30L02	24°	4.0	
	LL01CR-ZE45L02	46°	1.1	
	LL01CR-ZE20L02	20°	4.7	
	LL01CR-ZE30L02	24°	3.9	
	LL01CR-ZE45L02	47°	1.1	
	LL01CR-ZE20L02	18°	5.8	
	LL01CR-ZE30L02	18°	6.3	
	LL01CR-ZE45L02	-	-	-
	LL01CR-ZE20L02	18°	5.9	
	LL01CR-ZE30L02	-	-	-
	LL01CR-ZE45L02	-	-	-

Product Nomenclature

Ledlink Led Type Lens Angle Holder

LL 01 CR- ZE 20 L02- U2- T

Lens Dot Number Serial Number Type of Material Tape

Ledlink Optics, Inc

Taiwan HQ

15F, No.655,Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.6, Gaoxin Road, Tiankeng, Hengli Town, Dongguan City,
Guangdong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com

