



Datasheet

LL01ED-AYxxL06-M2

Available Distribution




LED



Recommend Applications



General Information




- Lens Material PMMA
- Lens Color Transparent
- Operating Temperature -40°C~+70°C
- Light Transmission Rate 400nm~900nm > 90%
- ✓ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- ⚠ Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Dimensions

Part Number	Diameter	Height
LL01ED-AYxxL06	Ø43.8	24.22
LL01ED-AYxxL06-M2	Ø46	27.1

*All dimensions are in millimeters.

Packaging Details (SPQ)



Accessories




- Available with Holder LL01ED0010Hx

Mechanical Specification

*All dimensions are in millimeters.


Lens Dimension

LL01ED-AY××L06



Holder Dimension

LL01EDOO10H×




Assembly Instruction

Fixing Method

Part No LL01ED-AY××L06-M2
Holder LL01EDOO10H×



Luminaire Accessories




Assembly Instruction

Fixing Method

Part No LL01ED-AY××L06-M2
Holder LL01EDOO10H×



Luminaire Accessories




Assembly Instruction

Fixing Method

Part No LL01ED-AY××L06



Luminaire Accessories




Assembly Instruction

Fixing Method

Part No LL01ED-AY××L06



Luminaire Accessories









Photometric Distribution







LED



10°









38°









LED



10°






38°






LED




10°



38°



Details by LED

Part No	Holder	LED Package Size	LED
LL01ED-AYxxL06	-	LES Ø8~16 / 3535 / 5050 / 7070	
LL01ED-AYxxL06-M2	 LL01ED0010Hx	LES Ø6 7070 / 9090	

LED	Part No	FWHM	cd / lm	IES
	LL01ED-AY10L06	17°	5.6	
	LL01ED-AY38L06	21°	3.9	
	LL01ED-AY10L06	19°	4.0	
	LL01ED-AY38L06	22°	3.2	
	LL01ED-AY10L06	20°	3.9	
	LL01ED-AY38L06	22°	3.2	
	LL01ED-AY10L06	20°	3.4	
	LL01ED-AY38L06	21°	3.4	
	LL01ED-AY10L06	25°	2.8	
	LL01ED-AY38L06	24°	2.4	
	LL01ED-AY10L06	12°	7.7	
	LL01ED-AY38L06	14°	7.2	
	LL01ED-AY10L06	16°	5.6	
	LL01ED-AY38L06	17°	4.9	
	LL01ED-AY10L06	9°	12.5	
	LL01ED-AY38L06	11°	9.4	

LED	Part No	FWHM	cd / lm	IES
	LL01ED-AY10L06	7°	19.0	
	LL01ED-AY38L06	11°	11.3	
	LL01ED-AY10L06	13°	8.2	
	LL01ED-AY38L06	15°	6.2	
	LL01ED-AY10L06	19°	4.4	
	LL01ED-AY38L06	20°	3.8	
	LL01ED-AY10L06	19°	4.5	
	LL01ED-AY38L06	21°	3.4	
	LL01ED-AY10L06-M2	15°	7.1	
	LL01ED-AY38L06-M2	20°	4.5	
	LL01ED-AY10L06-M2	16°	6.0	
	LL01ED-AY38L06-M2	18°	4.8	
	LL01ED-AY10L06-M2	16°	6.2	
	LL01ED-AY38L06-M2	19°	3.8	

Product Nomenclature

Ledlink Led Type Lens Angle Holder
LL 01 ED- AY 10 L06 -M2
Lens Dot Number Serial Number Type of Material

Ledlink Optics, Inc

Taiwan HQ

15F, No.655,Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.6, Gaoxin Road, Tiankeng, Hengli Town, Dongguan City,
Guangdong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com

