



PLETRONICS OeDA Series OeXO® Oscillator



OeDA
5.0 x 3.2 x 1.85 mm
LCC Ceramic Package

Features

- Temperature Compensated Crystal Oscillator
- Voltage Control Function option
- Low Power / Fast Warm Up
- CMOS Output or Clipped Sine Output
- 2.5V ~ 3.3V Nominal Supply Voltage

Applications

- SONET / SDH / DWDM
- Test & Measurement
- Telecom Transmission & Switching Equipment
- Base Stations / Picocell
- Wireless Communication Equipment

Electrical Characteristics for HCMOS

Parameter	Min	Typ	Max	Unit	Condition (Consult factory for other options)
Frequency Range ²	8.192	-	40.0	MHz	See table below for developed frequencies
Frequency Stability vs. Temperature ²	-	-	±200	ppb	Over -40°C to +85°C
	-	-	±100		Over -10°C to +70°C
	-	-	±50		Over 0°C to +70°C
Frequency Initial Calibration		-	±2.0	ppm	Vcontrol 1.50 volts at 25°C ± 2°C if Vcontrol option used
Operable Temperature Range ²	0 -10 -40	-	+70 +70 +85	°C	
Supply Voltage ^{1,2} V _{CC}	2.5	-	3.3	V	± 5%
Supply Current ² I _{CC}	-	3.5 4.5 6.5	-	mA	10 MHz 25 MHz 40 MHz Load: 15 pF, V _{CC} ± 5%
Frequency Stability vs. Supply	-	-	±0.2	ppm	Load: 15 pF, V _{CC} ± 5%
Frequency Stability vs. Load	-	-	±0.2	ppm	Load: 15 pF ± 10%
Vcontrol Range	0.5	-	2.5	V	1.50 volts nominal
Frequency Pullability ² (VCTCXO)	±5	-	-	ppm	Positive Slope
Linearity	-	-	±2.0	%	
Output Waveform	CMOS				
Duty Cycle	40	50	60	%	Load: 15 pF V _{th} : T _R and T _F 10% and 90% of V _{CC} V _{th} : D.C. 50% of V _{CC}
Output V _{HIGH}	90	-	-	%V _{CC}	
Output V _{LOW}	-	-	10	%V _{CC}	
Output T _{RISE} and T _{FALL}	-	-	6.5	nS	
Startup Time	-	-	10.0	μs	Within ± 2.0 ppm of final frequency
Output Enable (Pad 5) V _{IH}	0.7V _{CC}	-	-	V	Output Active (If Pad 5 open output also active)
Output Disable (Pad 5) V _{IL}	-	-	0.3V _{CC}	V	Output disabled to Hi-Z state
Long Term Stability (Aging)	-	-	±1.0	ppm	First year at 25°C ± 2°C
Phase Noise	100 Hz 1 kHz 10 kHz 100 kHz 1 MHz	-	-122 -142 -154 -157 -159	-	dBc/Hz 25°C ± 2°C at 20.0 MHz
Jitter	-	0.3	-	ps	Frequency offset from carrier 12 kHz to 5 MHz Typical performance at 20.0 MHz
Storage Temperature Range	-55	-	+95	°C	

Note: ¹ Place a 10nF power supply bypass capacitor next to device for correct operation

² Typical capabilities shown. A unique OeXO® datasheet is created for each specific device. See Factory for other options.

Product information is current as of publication date. The product conforms to specifications per the terms of the Pletronics standard warranty. **May 31, 2024 Rev. G**
Production processing does not necessarily include testing of all parameters.



PLETRONICS OeDA Series OeXO® Oscillator

Electrical Characteristics for Clipped Sine Wave

Parameter	Min	Typ	Max	Unit	Condition (Consult factory for other options)		
Frequency Range ²	8.192	-	40.0	MHz	See table below for developed frequencies		
Frequency Stability vs. Temperature ²	-	-	±200	ppb	Over -40°C to +85°C	at fixed V _{CC} + load (reference to midpoint min/max frequency) See factory for other options	
	-	-	±100		Over -10°C to +70°C		
	-	-	±50		Over 0°C to +70°C		
Frequency Initial Calibration		-	±2.0	ppm	V _{control} 1.50 volts at 25°C ± 2°C if V _{control} option used		
Operating Temperature Range ²	0 -10 -40	-	+70 +70 +85	°C			
Supply Voltage ^{1,2} V _{CC}	2.5	-	3.3	V	± 5%		
Supply Current ² I _{CC}	-	2.5 3.0 4.0	-	mA	10 MHz 25 MHz 40 MHz	Load: 10 Kohm 10 pF, V _{CC} ± 5%	
Frequency Stability vs. Supply	-	-	±0.2	ppm	V _{CC} ± 5%		
Frequency Stability vs. Load	-	-	±0.2	ppm	Load: 10 Kohm 10 pF ± 10%		
V _{control} Range	0.5	-	2.5	V	1.50 volts nominal		
Frequency Pullability ²	±5	-	-	ppm	Positive Slope		
Linearity	-	-	±2.0	%			
Output Waveform	Clipped Sine Wave				DC Coupled		
Output Level	0.8	-	-	V _{p-p}	Load: 10 Kohm 10 pF ± 10%		
Startup Time	-	-	10.0	ms	Within ± 2.0 ppm of final frequency		
Output Enable (Pad 5) V _{IH}	0.7V _{CC}			V	Output Active (If Pad 5 open output also active)		
Output Disable (Pad 5) V _{IL}			0.3V _{CC}	V	Output disabled to Hi-Z state		
Long Term Stability (Aging)	-	-	±1.0	ppm	First year at 25°C ± 2°C		
Phase Noise	100 Hz 1 kHz 10 kHz 100 kHz 1 MHz	-	-122 -142 -154 -157 -159	dBc/Hz	25°C ± 2°C at 20.0 MHz		
Jitter	-	0.3	-		Frequency offset from carrier 12 kHz to 5 MHz Typical performance at 20.0 MHz		
Storage Temperature Range	-55	-	+95	°C			

Note: ¹ Place a 10nF power supply bypass capacitor next to device for correct operation

² Typical capabilities shown. A unique OeXO® datasheet is created for each specific device. See Factory for other options.

The following is a list of developed frequencies. Consult factory for other options.

10.0M, 14.4, 16.384M, 19.2M, 20.0M, 25.0M, 26.0M, 28.8M, 40.00M



PLETRONICS OeDA Series OeXO® Oscillator

Part Number (Possible Options shown)

Series Model	V _{CC} Supply Voltage ¹	Operating Temperature		Stability ^{1,2}	Pullability ¹	Frequency
		Lowest	Highest	(ppm)	(ppm)	(MHz)
OEDA	A unique number will be assigned for your exact specification					-20.0M
	3.3 volts nominal 3.0 volts nominal 2.8 volts nominal 2.5 volts nominal	0°C -10°C -40°C	+70°C +85°C	± 0.05 ± 0.1 ± 0.2	0 (TCXO) ± 5 ± 8	8.192 - 40 MHz

¹ Contact Factory for non-standard specifications

² Not all stabilities are available with all operating temperature ranges. Contact Factory for exact combinations available.

Device Marking

FFFF.zzz YMD • PLEzzzzz YMD	OR	FFFF. zzz • P zzz zz YMD
--------------------------------------	----	-----------------------------

FFFF = Crystal Frequency in MHz (See Note below)

z = Internal factory codes

PLE = Pletronics

YMD = Date code (may appear in one of 3 locations shown)

Note: Output Frequency may be half the Crystal Frequency marking, depending on requirements.

Specifications such as part number, frequency stability, supply voltage and operating temperature range, etc. are not identified from marking. External packaging labels and packing list will correctly identify the ordered Pletronics part number.

Codes for Date Code YMD (Year Month Day)

Code	3	4	5	6	7	Code	A	B	C	D	E	F	G	H	J	K	L	M
Year	2023	2024	2025	2026	2027	Month	JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC

Code	1	2	3	4	5	6	7	8	9	A	B	C	D	E	F	G	H	J	K	L	M	N	P	R	T	U	V	W	X	Y	Z
Day	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31

Package Labeling


P/N Label is 1" x 2.6" (25.4mm x 66.7mm)

Font is Courier New

Bar code is 39-Full ASCII

RoHS Label is 1" x 2.6" (25.4mm x 66.7mm)

Font is Arial



Pletronics Inc. certifies this device is in accordance with the RoHS and REACH directives.


Pletronics Inc. guarantees the device does not contain the following: Cadmium, Hexavalent Chromium, Lead, Mercury, PBB's, PBDE's

Weight of the Device: 0.10 grams

Moisture Sensitivity Level: 1 As defined in J-STD-020D

Second Level Interconnect code: e4

Mechanical Dimensions




Dimensions in mm

Pin Connections

Pin	Function
1	Voltage Control (VCTCXO) Gnd/NC (TCXO)
2	NC
3	NC
4	Ground
5	Enable/Disable
6	Output
7	Vc Filter (optional)
8	NC
9	Vcc
10	Ground

Enable/Disable	
Pin 5	Output
VIH or Open	Active
VIL or Gnd	Disabled - Tristate



Pad Layout
Disclaimer: Recommended layout shown. Adjust layout as needed for individual process requirements.


Contacts (pads): Gold (0.3 to 1.0 μ m) over Nickel 1.27 to 8.89 μ m

For Optimum Jitter Performance, Pletronics recommends:



- A ground plane under the device
- Do not route large transient signals (both current and voltage) under the device
- Do not place near a large magnetic field such as a high frequency switching power supply
- Do not place near piezoelectric buzzers or mechanical fans
- Minimize air flow across the device

Electrical Test /Load Circuit

Clipped Sine Wave



CMOS



Environmental / ESD Ratings

Reliability: Environmental

Parameter	Condition
Mechanical Shock	MIL-STD-883, Method 2002, Condition B
Vibration	MIL-STD-883, Method 2007, Condition A
Solderability	IPC J-STD-002
Thermal Cycle	MIL-STD-883 Method 1010, Condition B

ESD Rating

Model	Min. Voltage	Condition
Human Body Model	2000V	JESD22-A114
Machine Model	200V	JESD22-A115


Thermal Characteristics:

Thermal Characteristics: The maximum die or junction temperature is 125°C

Absolute Maximum Ratings


Parameter	Unit
V_{CC} Supply Voltage	-0.6V to +4.6V
V_i Input Voltage	-0.6V to $V_{CC} + 0.6V$
I_o Output Current	-10mA to +10mA

Reflow Cycle



Tape and Reel

Tape and Reel available for quantities of 250 to 1000 per reel, cut tape for < 250. 12mm tape, 8mm pitch.



Tape Variable Dimensions Table 2							
Tape Size	E2 typ	F	P1	W max	Ao	Bo	Ko
12mm	10.25 ±0.05	8.0 ±0.1	12.2	3.5±0.1	5.3±0.1	1.9±0.1	

Dimensions in mm Drawing Not to scale

Note 1: Embossed cavity to conform to EIA-481-B

Reel Size	A		B		C	D
	Inches	mm	Inches	mm	mm	mm
7	7.0	180	2.50	60	13.0 +0.4 +0.5 -0.2	Tape size +2.0 -0.0

Tape Constant Dimensions Table 1

Tape Size	Do	D1 min	E1	Po	P2	T max	T1 max
12mm	1.5 +0.1 -0.0	1.5	1.75 ±0.1	4.0 ±0.1	2.0 ±0.05	0.3	0.1

Product information is current as of publication date. The product conforms to specifications per the terms of the Pletronics standard warranty. Production processing does not necessarily include testing of all parameters.



PLETRONICS OeDA Series OeXO® Oscillator

Important Notice

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, weapons, weapon systems or space applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics, Inc.
19013 36th Ave. West
Lynnwood, WA 98036-5761
U.S.A.

Tel: 425.776.1880
Fax: 425.776.2760
email: ple-sales@pletronics.com
URL: www.pletronics.com