


# Datasheet



**TAOGLAS®**

## LAN Transformer 1G Base-T PoE Ultra

**Part No:**  
**TMU24C14U**

**Description:**  
1G Base-T transformer  
Single Port and 24pin SMT

**Features:**  
PoE Ultra  
3Wire + Transformer  
Industrial grade

1. Introduction	3
2. Specifications	4
3. Mechanical	5
4. Electrical	6
5. Packaging	7
Changelog	8

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Ireland  
ISO 9001: 2015  
Certified



Taiwan  
ISO 9001: 2015  
Certified



QUALITY MANAGEMENT SYSTEM  
IATF16949

## 1. Introduction



Featuring a compatible footprint with industry LAN transformers, and designed to work in demanding industrial environmental conditions, the Taoglas TMU24C14U is a 1G Base-T Single Port of 24pin with 3Wire and Transformer which makes it suitable for PoE Ultra (1100mA) applications in Industrial environments.

Typical applications for this cost-effective part are:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

The Taoglas Magnetics Product Team have over fifteen years of LAN magnetics design and high-quality manufacturing. With an ever-expanding portfolio, we provide trusted products and services to customers within a wide range of applications such as: Networking and Interconnect Devices, Servers, Switches, Router, Communication systems and any Digital Consumer electronics.

The Taoglas Exos Series offer an extensive product line of LAN Transformers designed for commercial and industrial grade applications, supporting 10/100 Base-T (Exos100 Series), 1G Base-T (Exos1G Series) and 10G Base-T (Exos10G Series). These products include Single, Dual, and Quad configurations not only for standard applications but also for Power over Ethernet (PoE, PoE+, PoE++).

For more information on the range of products or for assistance with integration, contact your regional Taoglas customer support team.

## 2. Specifications

Electrical Performance @25°C		
Inductance OCL	350uH Min. @100KHz/0.1V with 18mA DC Bias	
Turns Ratio ( $\pm 3\%$ )	TX=1CT: 1CT	RX=1CT: 1CT
LK:	0.5uH Max @100KHz/0.2V	
Cw/w	35PF Max @100KHz/0.2V	
D.C.R:	1.2-ohm Max	
Insertion Loss	-1.5dB Max@1-250MHz -3.0dB Max@250-500MHz	
Return Loss	1-40MHz: -16dB Min 40-100MHz: -10+20*log(f/80) dB Min	
Crosstalk	1-100MHz: -30dB Min	
CMRR	1-100MHz: -30dB Min	
DC Current Rating	1100mA DC Max @57V	
Hi-Pot	1500Vrms	


Environmental Specifications	
Operating Temperature	-40°C TO +85°C

Compliance	
UL recognized - FILE NO. E528697	
RoHS Compliant	

Storage requirements	
Humidity	MSL - 1
Storage Temperature	-40°C TO +125°C

## 3. Mechanical

### 3.1 Mechanical Drawings




#### Mechanical Specifications

Length	17.6 mm
Width	16 mm
Height	6 mm
Mounting Style	Surface Mount (SMT)

Dimensions are in millimeters with the following tolerances: X.XX = ±0.25

### 3.2 Pad Layout




Suggested pad layout


Dimensions are in millimeters with the following tolerances: X.XX = ±0.10

## 4. Electrical

### 4.1 Electrical Drawings



### 4.2 Profile of Reflow Solder




## 5. Packaging

### 5.1 SPQ

1 reel = 400 pcs

Reel (mm): 32x14.2x17.3

Weight (gr): 950



1 Carton = 7 reels = 2800 pcs

Carton dimensions: 373\*365\*284 mm

Carton Weight: 8.05kg



### 5.1 SPQ

Taoglas Limited	
P/N NO: XXXXXXXX	
QYT: XXX PCS	DC: XXXX
DATE: XXXX-XX-XX	

**SPQ Label (8x5cm)**

Taoglas Limited	
P/N NO: XXXXXXXX	
PO: XXXXXXXX	B/N: XXXXXXXX
QYT: XXX PCS	DC: XXXX
DATE: XXXX-XX-XX	

**Carton Label (8x5cm)**

# Changelog

Changelog for the datasheet

**SPE-23-8-054 – TMU24C14U**

**Revision: B (Current Version)**

Date: 2025-10-21

Notes: Updated electrical drawing.

Author: Paul Liu

**Previous Revisions**

**Revision: A (Original First Release)**

Date: 2023-03-30

Notes:

Author: Javier Vasena



**TAOGLAS.**<sup>®</sup>

[www.taoglas.com](http://www.taoglas.com)