

**IE-C5DD4UG0050MCSMCS-E****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Assembled IE cables, PROFINET, Cat. 5, PUR, green, drag-chain compatible, M12

**General ordering data**

|            |                                                                                                                                                   |
|------------|---------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Dragline cable, PROFINET, M12 D-code – IP 67 straight pin, M12 D-code – IP 67 straight pin, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 5 m |
| Order No.  | <a href="#">1025950050</a>                                                                                                                        |
| Type       | IE-C5DD4UG0050MCSMCS-E                                                                                                                            |
| GTIN (EAN) | 4032248775675                                                                                                                                     |
| Qty.       | 1 pc(s).                                                                                                                                          |

Creation date June 14, 2025 3:26:17 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

## IE-C5DD4UG0050MCSMCS-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Length     | 5 m      | Length (inches) | 196.85 inch |
| Net weight | 300.08 g |                 |             |

## Temperatures

|                          |                |                       |                |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature      | -50 °C...70 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -20 °C...60 °C |                       |                |

## Cable specific standards

|                               |                                                   |                              |                          |
|-------------------------------|---------------------------------------------------|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |                              |                          |

## General standards

|                         |         |                    |                 |
|-------------------------|---------|--------------------|-----------------|
| Certificate no. (cULus) | E316369 | Connector standard | IEC 61076-2-101 |
|-------------------------|---------|--------------------|-----------------|

## Standards

|                              |                          |                               |                                                   |
|------------------------------|--------------------------|-------------------------------|---------------------------------------------------|
| Connector standard           | IEC 61076-2-101          | Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) |
| Standard, shielding material | DIN EN 13602 Cu-ETP-A..B | Standard, wire material       | DIN EN 13602 Cu-ETP-A                             |

## Cable structure

|                              |                                                         |                                       |                                                   |
|------------------------------|---------------------------------------------------------|---------------------------------------|---------------------------------------------------|
| Arrangement of wire cores    | Star-quad                                               | Colour sequence or wires - wire pairs | white, yellow, blue, orange                       |
| Complete shielding           | Aluminium foil, Shielding braid made from copper wiring | Cross-section                         | 4*AWG 22/7 - 0.32 mm <sup>2</sup>                 |
| Diameter of inner sheathing  | 3.9 mm                                                  | Filler                                | As central element                                |
| Insulation                   | PE                                                      | Insulation cross-section              | 1.5 mm                                            |
| Material sheath              | PUR                                                     | Number of wires                       | 4                                                 |
| Overlap of shielding braid   | 85 %                                                    | Sheath diameter, max.                 | 6.7 mm                                            |
| Sheath diameter, min.        | 6.3 mm                                                  | Sheathing colour                      | green (RAL 6018)                                  |
| Sheathing material thickness | 0.9 mm                                                  | Shielding                             | SF/UTP                                            |
| Shielding braid thickness    | 0.13 mm                                                 | Standard designations                 | 2YH(ST)C11Y<br>2x2x0.75/1.5-100 LI VZN<br>GN FRNC |
| Strands                      | 7                                                       | Wire core insulation thickness        | 0.38 mm                                           |
| Wire material                | Stranded tin-plated copper wire                         |                                       |                                                   |

## Electrical properties of cable

|                                |                                      |                               |                                             |
|--------------------------------|--------------------------------------|-------------------------------|---------------------------------------------|
| Capacity at 1 kHz              | 52 nF/km                             | Category                      | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) |
| Characteristic impedance       | 100 ± 15 Ω at 1-100 MHz              | Delay skew                    | 40 ns/100m                                  |
| Loop resistance                | 120 Ω/km                             | Operating voltage (UL rating) | 600 V                                       |
| Operating voltage, UL          | 600 V                                | Resistance differential       | 3 %                                         |
| Signal propagation time        | 5.3 ns/m                             | Speed                         | 180 m/min                                   |
| Test voltage: wire-wire-shield | 2000 V <sub>eff</sub> , 50 Hz, 1 min | Transfer impedance            | 20 mΩ/m at 10 MHz                           |

Creation date June 14, 2025 3:26:17 PM CEST

## IE-C5DD4UG0050MCSMCS-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Mechanical and material properties of cable

|                                 |                                        |                                |                                |
|---------------------------------|----------------------------------------|--------------------------------|--------------------------------|
| Abrasion resistance             | very good                              | Acceleration                   | 4 m/s <sup>2</sup>             |
| Bending cycles                  | 3 Mio                                  | Fire propagation               | No                             |
| Halogen                         | halogen-free, according to IEC 60754-2 | Min. bending radius, once only | 5 x cable diameter             |
| Min. bending radius, repetitive | 7.5 x cable diameter                   | Pulling force                  | ≤ 150 N                        |
| Resistance to oils              | in accordance with IEC 60811-2-1       | Resistance to spread of flame  | in accordance with IEC 60332-1 |
| Silicone-free                   | Yes                                    | Speed                          | 180 m/min                      |
| UV-resistant                    | Yes                                    |                                |                                |

## Plug, left

|           |                                                                     |
|-----------|---------------------------------------------------------------------|
| Plug left | M12, D-coded, IP67, male contact, straight, plug, Plastic, shielded |
|-----------|---------------------------------------------------------------------|

## Plug, right

|            |                                                                     |
|------------|---------------------------------------------------------------------|
| Plug right | M12, D-coded, IP67, male contact, straight, plug, Plastic, shielded |
|------------|---------------------------------------------------------------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002599    | ETIM 7.0    | EC002599    |
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 9.0  | 27-06-03-08 |
| ECLASS 9.1  | 27-06-03-08 | ECLASS 10.0 | 27-06-03-08 |
| ECLASS 11.0 | 27-06-03-08 | ECLASS 12.0 | 27-06-03-08 |
| ECLASS 13.0 | 27-06-03-08 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 67cf1078-beca-4687-860b-dc475a6ec24a |

## Approvals

Approvals



|                         |                                                                                                                                                                             |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID         | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319228/-T1z1mm-S800/</a> |
| ROHS                    | Conform                                                                                                                                                                     |
| UL File Number Search   | UL Website                                                                                                                                                                  |
| Certificate no. (cULus) | E316369                                                                                                                                                                     |

## IE-C5DD4UG0050MCSMCS-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

## Downloads

|                                                  |                                                                                                                                                            |
|--------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Con-<br>formity | <a href="#">DUXR.E316369</a><br><a href="#">PROFINET Manufacturer's Declaration</a>                                                                        |
| Engineering Data                                 | <a href="#">CAD data – STEP</a>                                                                                                                            |
| User Documentation                               | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>                                                                                         |
| Catalogues                                       | <a href="#">Catalogues in PDF-format</a>                                                                                                                   |
| Brochures                                        | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a><br><a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |

### IE-C5DD4UG0050MCSMCS-E

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Wiring

|     |        |     |
|-----|--------|-----|
| M12 |        | M12 |
| 1   | yellow | 1   |
| 2   | white  | 2   |
| 3   | orange | 3   |
| 4   | blue   | 4   |