


FEC ACCELERATOR SERVER ADAPTER BASED ON INTEL® VRAN
 DEDICATED ACCELERATOR ACC100

PCIe-ACC100

Datasheet



Features


- Integrates Intel® vRAN Dedicated Accelerator ACC100 eASIC device (formerly Mount Bryce)
 - LDPC FEC processing (3GPP 5G): LDPC encode/decode, CRC, rate matching, HARQ
 - LTE FEC processing (3GPP 4G): Turbo encode/decode, CRC, rate matching
 - Supports virtualization, scalable to desired system configuration; separate engines for UL/DL
 - Load balancing supported by Queue Mgr.
- Low profile PCIe card for low-cost design
 - Power envelope of low-profile slot
 - For Intel® Xeon® Scalable Processor & Xeon® D Processor based COTS servers
 - No PCIe card auxiliary power required
 - No front-panel I/O for maximum air-flow Full and Half-height bracket options
- Onboard DDR4 for HARQ processing
- High-speed host interface: PCIe x16 Gen3
- Operating temperature: -5°C to +55°C
- Passive cooling
- NEBS compliance ready

Specifications

Dimensions	Half-Height Half-Length (HHL) board Option 1: with full-height bracket: 169.4mm x 21.59mm x 119.96mm Option 2: with half-height bracket: 169.26mm x 22mm x 80mm
Performance	5G throughput: Encode = 21Gbps encode, 8Gbps decode 4G throughput: Encode = 8.4Gbps encode, 2.1Gbps decode
Software and Cloud Support	Interface via DPDK BBDev Cloud native, VM and bare metal, SRIOV/Vt-d
Interface	PCIe x16 Gen3 interface to host
Memory	DDR4-2666 4GB ECC
Operating Temperature	-5°C - +55°C

Mechanical Overview

Option 1: Full-height bracket



Option 2: Half-height bracket

