

**WQV 70/95/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

|            |  |
|------------|--|
| Version    | Cross-connector (terminal), when screwed in, Silver grey, 232 A, Number of poles: 3, Pitch in mm (P): 27.00, Insulated: No, Width: 10 mm |
| Order No.  | <a href="#">1063600000</a>   |
| Type       | WQV 70/95/3  |
| GTIN (EAN) | 4008190187514  |
| Qty.       | 5 pc(s).   |

Creation date June 14, 2025 4:32:13 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

## WQV 70/95/3

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 61.6 mm | Depth (inches)  | 2.425 inch |
| Height     | 54 mm   | Height (inches) | 2.126 inch |
| Width      | 10 mm   | Width (inches)  | 0.394 inch |
| Net weight | 159.8 g |                 |            |

### Temperatures

|                     |                |                     |               |
|---------------------|----------------|---------------------|---------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -5 °C...40 °C |
|---------------------|----------------|---------------------|---------------|

### Material data

|          |               |        |             |
|----------|---------------|--------|-------------|
| Material | tinned copper | Colour | Silver grey |
|----------|---------------|--------|-------------|

### System specifications

|         |                   |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

### Additional technical data

|                |                 |
|----------------|-----------------|
| Type of fixing | when screwed in |
|----------------|-----------------|

### Conductors for clamping (rated connection)

|                         |      |
|-------------------------|------|
| Tightening torque, max. | 3 Nm |
|-------------------------|------|

### Cross-connector

|                                     |                 |                           |       |
|-------------------------------------|-----------------|---------------------------|-------|
| Number of cross-connected terminals | 3               | Rated current, multi-pole | 232 A |
| Type                                | Cross-connector |                           |       |

### Dimensions

|                 |       |
|-----------------|-------|
| Pitch in mm (P) | 27 mm |
|-----------------|-------|

### General

|                 |   |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

### Rating data

|               |       |
|---------------|-------|
| Rated current | 232 A |
|---------------|-------|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ETIM 10.0   | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |
| ECLASS 13.0 | 27-25-03-03 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 |             |             |

## WQV 70/95/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Technical data

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks<br/>Instruction</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                        |
| Brochures          |   |