

# Ethernet

Featured Products


Ethernet Transceivers (PHYs)

Ethernet Switches

## Featured Products

# MxL86252, MxL86282

5- and 8-port 2.5G Ethernet Switches with Integrated PHYs and 2.5G & 10G Uplinks



### Key Features

- Integrated 10/100/1000/2.5GBASE-T PHYs (5 or 8 ports)
- Two optional 10G uplink ports
- Power: <700mW per PHY
- 400MHz ARC CPU: Web smart
- Unlocking wire speed switching
- VLAN, QinQ, QoS, traffic shaping, ...
- BGA-277 12x12mm, 0.628mm pitch

### Benefits




- Low-power consumption through high integration
- Power saving modes for short cables, through Energy Efficient Ethernet (EEE) and no-link detection
- Integrated processor enables web-smart switch applications

### Applications

- Standalone five or eight-port 2.5G switches
- Eight-port SMB switches with two 10G uplinks
- Five-port SMB switches with 10G and 2.5G uplinks
- Unmanaged and web-smart switches
- External switches for gateway SoCs

### Standards


- IEEE Standard for Ethernet, IEEE 802.3™-2022



MxL86282 Block Diagram


# Ethernet Transceivers (PHYs)

Product	Ethernet Ports	Ethernet Bandwidth (Mbps)	Interfaces	MACsec	1588v2	SyncE	EEE	Thermal Protection	Min Temp (°C)	Max Temp (°C)	Package (X x Y mm)	Evaluation Board/s
MxL86288L	8	10, 100, 1000, 2500	2 x USXGMII-M		•	•	•	•	0	70	BGA-256 (13x13)	MxL86288L-EVK-1
MxL86288I	8	10, 100, 1000, 2500	2 x USXGMII-M		•	•	•	•	-40	85	BGA-256 (13x13)	
GPY245	4	10, 100, 1000, 2500	SGMII+, USXGMII-M	•	•	•	•	•	-40	85	BGA-236 (12x12)	GPY245-EVK-1, GPY245-EVK-2
GPY241	4	10, 100, 1000, 2500	SGMII+, USXGMII-M		•	•	•	•	0	70	BGA-236 (12x12)	
GPY215	1	10, 100, 1000, 2500	SGMII+	•	•	•	•	•	-40	85	QFN-56 (7x7)	GPY215-EVK-1, GPY215-EVK-3
GPY211	1	10, 100, 1000, 2500	SGMII+		•	•	•	•	0	70	QFN-56 (7x7)	GPY215-EVK-1
MxL86211C	1	10, 100, 1000, 2500	SGMII+		•	•	•	•	0	70	QFN-40 (5x5)	MxL86211C-EVK-1
MxL86211I	1	10, 100, 1000, 2500	SGMII+		•	•	•	•	-40	85	QFN-40 (5x5)	
GPY115	1	10, 100, 1000	SGMII	•	•	•	•	•	-40	85	QFN-56 (7x7)	GPY215-EVK-1
MxL86110C	1	10, 100, 1000	RGMII		•	•	•	•	0	70	QFN-40 (5x5)	MxL86110I-EVK-1
MxL86110I	1	10, 100, 1000	RGMII		•	•	•	•	-40	85	QFN-40 (5x5)	
MxL86111C	1	10, 100, 1000	RGMII, RGMII/1000BASE-X/100BASE-FX		•	•	•	•	0	70	QFN-48 (6x6)	
MxL86111I	1	10, 100, 1000	RGMII, RGMII/1000BASE-X/100BASE-FX		•	•	•	•	-40	85	QFN-48 (6x6)	
MxL86112C	1	10, 100, 1000	SGMII		•	•	•	•	0	70	QFN-40 (5x5)	MxL86112C-EVK-1
MxL86112I	1	10, 100, 1000	SGMII		•	•	•	•	-40	85	QFN-40 (5x5)	



Router and Gateway Application

5 ~ 16  
2.5GbE LAN




N x Eight 2.5GBASE-T Ports


Enterprise Switch

# Ethernet Switches

Product	Ethernet Ports	Ethernet Bandwidth (Mbps)	Interface/Uplink Ports	Interfaces	Supply Voltage (V)	Web-Smart Support	1588v2	SyncE	EEE	Min Temp (°C)	Max Temp (°C)	Package (X x Y mm)	Evaluation Board
MxL86281S	16	10, 100, 1000, 2500	2	USXGMII	3.3/1.8/1.2/0.8	•			•	0	70	2x BGA-277 (12x12)	MxL86281S-EVK-1
MxL86282C	8	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8				•	0	70	BGA-277 (12x12)	MxL86282S-EVK-1
MxL86282I	8	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8	•			•	-40	85	BGA-277 (12x12)	
MxL86282S	8	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8	•	•	•	•	0	70	BGA-277 (12x12)	MxL86282S-EVK-1
MxL86252C	5	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8				•	0	70	BGA-277 (12x12)	MxL86252S-EVK-1
MxL86252I	5	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8	•	•	•	•	-40	85	BGA-277 (12x12)	
MxL86252L	5	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8				•	0	70	BGA-277 (12x12)	
MxL86252S	5	10, 100, 1000, 2500	2	XFI / USXGMII / SGMII+	3.3/1.8/1.2/0.8	•			•	0	70	BGA-277 (12x12)	
GSW145	4	10, 100, 1000	2	RGMII, SGMII+	3.3/1.1				•	-40	85	MRQFN-105 (8x8)	GSW145-EVK-1
GSW141	4	10, 100, 1000	2	RGMII, SGMII	3.3/1.1				•	0	70	MRQFN-105 (8x8)	
GSW140	4	10, 100, 1000	2	RGMII, SGMII+	3.3/1.1				•	0	70	MRQFN-105 (8x8)	
GSW125	2	10, 100, 1000	2	RGMII, SGMII+	3.3/1.1				•	-40	85	MRQFN-105 (8x8)	
GSW120	2	10, 100, 1000	2	RGMII, SGMII+	3.3/1.1				•	0	70	MRQFN-105 (8x8)	



Standalone Desktop Switch with Optional Brightness On/Off Switch



Home Gateway



**Corporate Headquarters:**  
 5966 La Place Court  
 Suite 100  
 Carlsbad, CA 92008  
 Tel.: +1 (760) 692-0711  
 Fax: +1 (760) 444-8598  
[www.maxlinear.com](http://www.maxlinear.com)

The content of this document is furnished for informational use only, is subject to change without notice, and should not be construed as a commitment, representation, or warranty by MaxLinear, Inc. or any of its affiliates (collectively, "MaxLinear"). MaxLinear assumes no responsibility or liability for any errors, omissions, or inaccuracies that may appear in the informational content contained in this document.

Reproduction, distribution, modification, or creation of derivative works, in part or in whole, without the prior written consent of MaxLinear is prohibited. MaxLinear, the MaxLinear logo, and any other MaxLinear trademarks (including but not limited to MxL, Full-Spectrum Capture, FSC, AirPHY, Puma, AnyWAN, VectorBoost, MXL WARE, and Panther) are all property of MaxLinear and/or one of its subsidiaries in the U.S.A. and other countries. All rights reserved. All third-party marks and logos are trademarks™ or registered® trademarks of their respective holders/owners.

© 2026 MaxLinear, Inc. All rights reserved.