

65W USB-C Laptop Charger, Compact GaN Wall Charger for Dell, XPS, HP ProBook, MacBook Pro, Microsoft Surface Pro, Black

Product ID: 1065NB-WALL-CHARGER



This USB-C power adapter with GaN delivers up to 65W of Power Delivery 3.0/2.0 power with broad voltage support (5V, 9V, 12V, 15V, 20V) and PPS profiles 5.0-16V4.0A (60W Max) and 5.0-21V3.25A (65W Max) for fast, safe charging of USB-C devices.

Designed for use with popular USB-C devices including Dell Pro/Plus, HP, HP ProBook, MacBook Pro, and Microsoft Surface Pro.

Built to keep both users and devices protected, it is cULus listed and FCC/ICES EMC and Japan PSE certified, with overvoltage, current, and temperature protection. Its efficient design meets DOE Level VI standards for energy efficiency.

Packaged with sustainability in mind, it features 75% postconsumer recycled (PCR) housing and FSCMix certified packaging. The compact packaging protects the product in transit while minimizing environmental impact.

Certifications, Reports and Compatibility



Applications

- Enables IT teams to standardize on a single 65W USB-C charger for enterprise laptop fleets, simplifying deployment and reducing accessory sprawl across Dell, HP, MacBook Pro, and Surface environments
- Provides a certified, energy-efficient power solution for regulated or corporate workspaces, ensuring safe, reliable laptop charging with globally recognized compliance standards

Features

- **Powerful, Fast, Universal Charging**: Delivers up to 65W of USB-C PD 3.0/2.0 power with broad voltage support (5V, 9V, 12V, 15V, 20V) to quickly and safely charge devices from smartphones to laptops, with a single, versatile GaN charger
- **Universal USB-C Charging for Leading Brands**: Designed for use with Dell Pro/Plus, HP ProBook, Apple MacBook Pro, and Microsoft Surface Pro; Supports PPS profiles 5.0-16V4.0A (60W Max) and 5.0-21V3.25A (65W Max) for fast, safe charging of USB-C devices
- **Safe, Reliable and Efficient**: cULus listed and FCC/ICES EMC and Japan PSE certified for global safety with over-voltage, current, and temp protection to keep both users and devices safe; Efficient design meets DOE Level VI standards
- **Reduces Packaging Waste**: Features 75% postconsumer recycled (PCR) housing and FSCMix certified packaging; Compact packaging protects the product in transit while minimizing environmental impact
- **The IT Pro's Choice**: Our power adapters offer a long-lasting, eco-conscious solution as manufacturers increasingly exclude chargers from new devices; Thoroughly tested in our Innovation Lab to ensure enterprise-grade reliability and operational safety

Hardware

Warranty	2 Years
Ports	1
Industry Standards	TUV Safety Listed (IEC 62368-1)
	USB Power Delivery 3.0

Connector(s)

Connector Type(s)	1 - NEMA 5-15 Power (North America)
-------------------	-------------------------------------

Power

Input Voltage	100 - 240 AC
Input Current	2.0A
Output Voltage	5V DC
	9V DC
	12V DC
	15V DC
	20V DC

Output Current	5.0A (Max)
Plug Type	USB Type-C (24 pin) USB Power Delivery Only
Power Consumption (In Watts)	65W

Environmental

Operating Temperature	0C to 25C (32F to 77F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	Operating 10% to 90% Storage 30% to 90%

Physical Characteristics

Color	Black
Product Length	2.2 in [56.3 mm]
Product Width	2.0 in [50.4 mm]
Product Height	1.1 in [28.7 mm]
Weight of Product	11.6 oz [329 g]

Packaging Information

Package Length	3.1 in [8.0 cm]
Package Width	3.7 in [9.3 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	4.2 oz [120.0 g]

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*