


DIMENSIONS(mm)			
SIZE	A \pm 0.38	B \pm 0.25	C \pm 0.25
14	44.00	36.00	25.50
24	54.70	46.70	36.20
36	67.70	59.70	49.00
50	82.70	74.70	64.50



RECOMMENDED P.C.B LAYOUT
36P SHOWN

SPECIFICATIONS:

ELECTRICAL:

CURRENT RATING:	1 AMPS
INSULATION RESISTANCE:	1,000 MΩ MIN. @ 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE:	1,000 VAC FOR 1 MINUTE
CONTACT RESISTANCE:	30 mΩ MAX.
OPERATING TEMPERATURE:	-55°C TO +105°C

MATERIALS:

INSULATION:	PBT, UL94 V-0 RATED
CONTACTS:	PHOSPHOR BRONZE
CONTACT PLATING:	GOLD FLASH IN MATING AREA
SHELL:	BRIGHT TIN IN SOLDER AREA STEEL, NICKEL PLATED

111-YYY-113L001

SERIES
 POSITIONS
 014
 024
 036
 050
 GENDER
 1 = MALE
 TERMINATION
 1 = DIP SOLDER
 SHELL PLATING
 3 = NICKEL
 HARDWARE
 00 = NO HARDWARE
 PLATING
 1 = GOLD FLASH

UNITS = mm

DO NOT SCALE FROM DRAWING




THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.


DRAWN:
WAYNE ROBBINS
DATE:
09/21/1998

NorComp


SCALE: NTS	1	2	REV 13
DWG NO.			111-YYY-113L001




14 POSITION



36 POSITION



24 POSITION



50 POSITION

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS
DATE:
09/21/1998

UNITS = inch

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 2	OF 2	REV 13
DWG NO. 111-YYY-113L001			