



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETERIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	MATERIAL / FINISH	WEIGHT / PC
UCSQ1-V316	316 STAINLESS STEEL	112.0 g (.247 lbs)
UCSQ1-VC	COMMERCIAL STEEL / GALVANIZED	113.5 g (.250 lbs)

#### NOTES:

1. PRIMARY DIMENSIONS IN METRIC (mm). DIMENSIONS IN [ ] ARE ENGLISH [ in ].
2. THIS PRODUCT INTENDED FOR USE WITH STRUT-TYPE LADDER RACK IN GALVANIZED STEEL, STAINLESS STEEL, OR ALUMINUM CONSTRUCTIONS.
3. EACH ASSEMBLY INCLUDES:
  - (1) TALL BRACKET PIECE
  - (1) CHANNEL NUT
  - (1) M8 X 1.25 X 20mm HEX HEAD CAP SCREW
  - (1) COMPRESSION SPRING



							TITLE UNICLIP STRUT-TYPE BRACKET UCSQ1						
							CUSTOMER DRAWING						
ITEM REVISION NAME	REMOVED 35.006 DIMENSION. UPDATED .XXX TOLERANCE REMOVED REVISION MARKERS								12L025AT/04		MATERIAL:  SEE CHART		
	D. DRAWING RECOVERY								12L025AT_DC/04D				
04D	10-22-24	ACC	KYWI	MRWA			006539/00				DRAWING NUMBER:  12L025AT_DC		
3	09-26-19	JBN	RGRO	JADE	D. DRAWING RECOVERY		12L025AT-DC						
2	07-22-14	JBN	RMHI	RGRO	C. REVISED COMPONENT CHANNEL NUT AFFECTING NOTE 3 AND PART WEIGHT		12L025AT-DC				DRAWING NUMBER:  12L025AT_DC		
-	-----	----	----	----	RELEASED TO PRODUCTION		-----						
1	06-17-14	RMHI	RMHI	RGRO	B. UPDATED WEIGHTS IN TABLE A. REVISED TITLE		12L025AT-DC				DRAWING NUMBER:  12L025AT_DC		
R	04-30-14	JBN	RMHI		DRAWING RELEASED								
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY	DATE	CHK	SCALE	SIZE	
								JBN	04-23-14	RMHI	N.T.S.	A	