



Series 11VR

11mm Panel Potentiometer

- Compact 11 mm package size
- Rotational life (15,000 cycles)
- Wide temperature range (-10°C to +70°C)
- Single and dual output options

Applications

- Consumer portable electronics
- Commercial appliances
- Instrument amplifiers and guitar effects
- Keyboards and synthesizers
- Communications equipment



Ordering Information

Series	Element	Terminal Configuration	Shaft Length	Shaft Trim	Mechanical Travel	Detent Option	Resistance Code	Resistance Taper																																									
11VR	1	H	20	F	2	N	103	B1																																									
		<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>X</td><td>Horizontal/Side Mount Bushingless, PC Pins, 10mm Height</td></tr><tr><td>H</td><td>Vertical/Rear Mount Thread Bushing, PC Pins</td></tr><tr><td>K</td><td>Vertical/Rear Mount Sleeve Bushing, PC Pins</td></tr><tr><td>Y</td><td>Horizontal/Side Mount Thread Bushing, PC Pins, 10mm Height</td></tr><tr><td>U</td><td>Vertical/Rear Mount Bushingless, PC Pins</td></tr></table>	Code	Spec.	X	Horizontal/Side Mount Bushingless, PC Pins, 10mm Height	H	Vertical/Rear Mount Thread Bushing, PC Pins	K	Vertical/Rear Mount Sleeve Bushing, PC Pins	Y	Horizontal/Side Mount Thread Bushing, PC Pins, 10mm Height	U	Vertical/Rear Mount Bushingless, PC Pins	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>B</td><td>Knurled (18 teeth)</td></tr><tr><td>F</td><td>Flatted</td></tr></table>	Code	Spec.	B	Knurled (18 teeth)	F	Flatted			<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>N</td><td>No Detent</td></tr><tr><td>C</td><td>Center Detent</td></tr></table>	Code	Spec.	N	No Detent	C	Center Detent			<table><tr><th>Code</th><th>Spec.**</th></tr><tr><td>A2</td><td>10% Log</td></tr><tr><td>A3</td><td>15% Log</td></tr><tr><td>B1</td><td>linear</td></tr><tr><td>C3</td><td>15% Antilog</td></tr></table>	Code	Spec.**	A2	10% Log	A3	15% Log	B1	linear	C3	15% Antilog						
Code	Spec.																																																
X	Horizontal/Side Mount Bushingless, PC Pins, 10mm Height																																																
H	Vertical/Rear Mount Thread Bushing, PC Pins																																																
K	Vertical/Rear Mount Sleeve Bushing, PC Pins																																																
Y	Horizontal/Side Mount Thread Bushing, PC Pins, 10mm Height																																																
U	Vertical/Rear Mount Bushingless, PC Pins																																																
Code	Spec.																																																
B	Knurled (18 teeth)																																																
F	Flatted																																																
Code	Spec.																																																
N	No Detent																																																
C	Center Detent																																																
Code	Spec.**																																																
A2	10% Log																																																
A3	15% Log																																																
B1	linear																																																
C3	15% Antilog																																																
<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>1</td><td>Single</td></tr><tr><td>2</td><td>Dual</td></tr></table>	Code	Spec.	1	Single	2	Dual	<table><tr><th>Code</th><th>Spec.*</th></tr><tr><td>12</td><td>12.5 mm</td></tr><tr><td>15</td><td>15 mm</td></tr><tr><td>17</td><td>17.5 mm</td></tr><tr><td>20</td><td>20 mm</td></tr><tr><td>22</td><td>22.5 mm</td></tr><tr><td>25</td><td>25 mm</td></tr><tr><td>27</td><td>27.5 mm</td></tr><tr><td>30</td><td>30 mm</td></tr></table>		Code	Spec.*	12	12.5 mm	15	15 mm	17	17.5 mm	20	20 mm	22	22.5 mm	25	25 mm	27	27.5 mm	30	30 mm	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>2</td><td>300°</td></tr></table>	Code	Spec.	2	300°	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>502</td><td>5kΩ</td></tr><tr><td>103</td><td>10kΩ</td></tr><tr><td>203</td><td>20kΩ</td></tr><tr><td>503</td><td>50kΩ</td></tr><tr><td>104</td><td>100kΩ</td></tr><tr><td>254</td><td>250kΩ</td></tr><tr><td>504</td><td>500kΩ</td></tr></table>		Code	Spec.	502	5kΩ	103	10kΩ	203	20kΩ	503	50kΩ	104	100kΩ	254	250kΩ	504	500kΩ
Code	Spec.																																																
1	Single																																																
2	Dual																																																
Code	Spec.*																																																
12	12.5 mm																																																
15	15 mm																																																
17	17.5 mm																																																
20	20 mm																																																
22	22.5 mm																																																
25	25 mm																																																
27	27.5 mm																																																
30	30 mm																																																
Code	Spec.																																																
2	300°																																																
Code	Spec.																																																
502	5kΩ																																																
103	10kΩ																																																
203	20kΩ																																																
503	50kΩ																																																
104	100kΩ																																																
254	250kΩ																																																
504	500kΩ																																																

* See shaft trim options for available lengths.

** Other JIS tapers are available. See charts.



Electrical Specifications

	Min	Typical	Max	Unit
Total Resistance Tolerance	-20	—	+20	%
Power Rating	—	+0.05	—	watt
Operating Voltage	—	—	+50 +20	VAC VDC
Residual Resistance	—	+30	—	Ω
Slider Noise	—	—	+100	mV
Tracking Error	Dual version only	-2	+2	dB
Insulation Resistance				
Single	500 VDC for 1 min.	+100	—	M Ω
Dual	250 VDC for 1 min	+100	—	M Ω
Dielectric Strength				
Single	500 VAC for 1 min., no arcing			
Dual	250 VAC for 1 min., no arcing			
Taper	Linear and audio options (see charts)			

Mechanical

Total Mechanical Travel	300° $\pm$ 5°
Operating Torque	30 to 200 gf-cm
Shaft Wobble	
Bushingsless	0.7 x L/20mm p-p max.; L = Shaft Length
With Bushing	0.7 x L/30mm p-p max.; L = Shaft Length
Shaft Push-Pull Strength	8 kgf for 3 sec.
Stop Strength	5 kgf-cm min.
Detent Position	150° $\pm$ 5°
Detent Torque	30 to 300 gf-cm
Rotational Life	15,000 cycles
Panel Nut Tightening Torque	10 kgf-cm
IP Rating	40
Mounting Hardware	One flat washer and one mounting hex nut supplied with bushing option
Packaging	Tray
Weight	3 grams

Environmental


	Min	Typical	Max	Unit
Operating Temperature	-10	—	+70	°C
Storage Temperature	-30	—	+70	°C
Soldering Conditions				
Wave Solder	Preheat: 100°C max for 2 min max; Solder temperature: 260°C $\pm$ 5°C for 5 sec max.;			
	No clean foam flux recommended			
Manual Solder	350°C $\pm$ 5°C for 3 sec max.; Sn95Ag5 no clean solder			
Wash	Not recommended			
Moisture Sensitivity Level	1			
ESD Classification (HBM)	Not applicable			

All testing is performed at room ambient conditions except as noted. Users should verify device actual performance in their specific applications
This product is compliant to RoHS3 Directive 2015/863 Amendments of Annex II on 31 March 2015, and REACH SVHC Directive EC 1907/2006 Amendments of Annex XIV & Annex XVII on 15 January 2018.



Custom and value-added options available on request. Please contact your sales representative for additional information.

Mechanical Specifications



Series 11VR Horizontal/Side Mount Bushingless (Single)



Series 11VR Vertical/Rear Mount Bushingless (Single)



CIRCUIT DIAGRAM




LENGTH	
L1	L2
20	7
22.5	7
25	12
27.5	12
30	12

Unit: mm


TOLERANCES UNLESS OTHERWISE SPEC	
$L \leq 10$	± 0.3
$10 < L \leq 100$	± 0.5
$100 < L$	± 0.8
ANGULAR DIMENSION	$\pm 5^\circ$

Mechanical Specifications

Series 11VR Horizontal/Side Mount with Threaded Bushing (Single)




Series 11VR Vertical/Rear Mount with Threaded Bushing (Single)




Mechanical Specifications

Series 11VR Vertical/Rear Mount Sleeve Bushing (Single)




Series 11VR Vertical/Rear Mount Sleeve Bushing (Dual)




Mechanical Specifications

Series 11VR Horizontal/Side Mount Bushingless (Dual)




Series 11VR Vertical/Rear Mount Bushingless (Dual)




Mechanical Specifications

Series 11VR Horizontal/Side Mount with Threaded Bushing (Dual)





Series 11VR Vertical/Rear Mount with Threaded Bushing (Dual)




Mechanical Specifications

18 Tooth Knurl Shaft Trim Option





LENGTH	
L1	L2
20	7
22.5	7
25	12
27.5	12
30	12



300° ROTATION

SHAFT SHOWN IN FULL CCW POSITION






LENGTH	
L1	L2
12.5	7
15	7
17.5	12
20	12
22.5	12
25	12
30	12

Unit: mm

Electrical Specification

Series 11VR Taper Graphs



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CTS:](#)

[11VR2Y25F2N103B1](#) [11VR2H25F2C103B1](#) [11VR1Y25F2N103B1](#) [11VR1U20F2C103B1](#) [11VR1H25F2C103B1](#)
[11VR2X20F2N103B1](#) [11VR2U20F2C103B1](#) [11VR1X20F2N103B1](#)