

PRO DM 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Use our diode and redundancy modules to connect two power supplies and compensate for a device failing. In addition, our capacity module offers power reserves, guaranteeing purposeful and quick triggering of a circuit breaker, for example.

General ordering data

Version	Diode module, 24 V DC
Order No.	2486070000
Type	PRO DM 10
GTIN (EAN)	4050118496772
Qty.	1 pc(s).

PRO DM 10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	125 mm	Depth (inches)	4.921 inch
Height	125 mm	Height (inches)	4.921 inch
Width	32 mm	Width (inches)	1.26 inch
Net weight	501 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
Humidity	5-95% relative humidity, T _u = 40°C, without condensation		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Input

Connection system	Screw connection	DC input voltage range	0...60 V DC
Input current	2 × 12 A (-40 °C ~ +45 °C), 2 × 10 A (+45 °C ~ +60 °C), 2 × 7.5 A (+70 °C)	Input fuse (internal)	No
Nominal power consumption	240 VA	Rated input voltage	24 V DC

Output

Connection system	Screw connection	Continuous output current @ U _{Nominal}	1 × 24 A (-40 °C ~ +45 °C), 1 × 20 A (+45 °C ~ +60 °C), 1 × 15 A (+70 °C)
Output current, max.	20 A	Output power	466 W
Protection against inverse voltage	Yes	Rated output voltage	V _{INPUT} -typ. 0.7 V
Residual ripple, breaking spikes	Dependent on the power supplies used		

General data

Degree of efficiency	> 97% @ 24 V Input voltage	Derating	> 60°C / 75% load @ 70°C
Housing version		Humidity	5-95% relative humidity, T _u = 40°C, without condensation
Mounting position, installation notice	Metal, corrosion resistant Horizontal on TS35 mounting rail. 50 mm of clearance at top & bottom for air circ. Can mount side by side with no space in between.	Operating temperature	-40 °C...70 °C
Short-circuit protection	No	Surge voltage category	III

PRO DM 10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

EMC / shock / vibration

Interference immunity test acc. to	EN 55022, EN 55024, EN 61000-3-2,-3, EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)	Shock resistance IEC 60068-2-27	
			30 g in all directions
Vibration resistance IEC 60068-2-6	2.3 g (on DIN rail)		

Insulation coordination

Insulation voltage input / earth	0.5 kV	Insulation voltage output / earth	0.5 kV
Pollution severity	2	Protection class	III, with no ground connection, for SELV
Surge voltage category	III		

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410		

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	10	Conductor cross-section, AWG/kcmil , min.	26
Conductor cross-section, flexible , min.	0.22 mm ²	Conductor cross-section, rigid , max.	6 mm ²
Conductor cross-section, rigid , min.	0.18 mm ²	Connection system	Screw connection
Wire connection cross section, flexible (input), max.	4 mm ²		

Connection data (output)

Conductor cross-section, AWG/kcmil , max.	10	Conductor cross-section, AWG/kcmil , min.	26
Conductor cross-section, flexible , max.	6 mm ²	Conductor cross-section, flexible , min.	0.22 mm ²
Conductor cross-section, rigid , max.	6 mm ²	Conductor cross-section, rigid , min.	0.18 mm ²
Connection system	Screw connection	Number of terminals	4 (++) / (-)

Approvals

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ECLASS 9.0	27-04-07-01
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-90	ECLASS 12.0	27-04-07-90

PRO DM 10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS	Conform
UL File Number Search	E258476

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format