

3M Science.
Applied to Life.™



NEW



3M™ Steel Barb Cable Ties

Industrial strength ties.

When the job calls for rugged cable management solutions that can withstand demanding conditions, you need cable ties you can trust. Introducing 3M™ Steel Barb Cable Ties, engineered to provide a tight, precise grip and a strong, long-lasting hold – even when the going gets tough.



A tough tie for tough jobs.

3M™ Steel Barb Cable Ties are made of high-quality nylon 6/6 and designed with a stainless-steel barb that, when engaged, presses into the strap and grips tight. The strap features a robust, ribbed pattern to help ensure your bundles stay intact, even in high vibration environments. And unlike typical ratchet-style cable ties, the barb can be locked at any point along the strap – allowing for more precise positioning. Plus, the rectangular head design includes rounded corners and a curved tip for easy, fast installation without snagging – critical when working in extreme conditions.

Features and Benefits

- Fast, tough hold for industrial applications
- Infinite locking positions to secure wire or cable
- Head design prevents snagging for fast, easy installation
- Ribbed body helps prevent slippage in high vibration environments
- Available in several strengths and lengths to cover your needs
- Colors available in natural for indoor use and UV weather-resistant black for indoor and outdoor use
- UL Listed 62275 Type 21 or 21S



3M Product	Size	UPC	Qty per Package	Packages per Case	MOQ/Case Qty (# Cable Ties)
------------	------	-----	-----------------	-------------------	-----------------------------

Natural

18 LB Steel Barb Tie

CTSB4NT18-C	4"	00076308925789	100	10	1000
CTSB8NT18-C	8"	00076308925826	100	10	1000

40 LB Steel Barb Tie

CTSB6NT40-C	6"	00076308925802	100	10	1000
-------------	----	----------------	-----	----	------

50 LB Steel Barb Tie

CTSB8NT50-C	8"	00076308925840	100	10	1000
CTSB8NT50-M	8"	00076308925864	1000	5	5000
CTSB11NT50-C	11"	00076308925888	100	10	1000
CTSB11NT50-M	11"	00076308925901	1000	5	5000
CTSB15NT50-C	15"	00076308925925	100	5	500
CTSB15NT50-M	15"	00076308925949	1000	5	5000

110 LB Steel Barb Tie

CTSB28NT110-L	28"	00076308926038	50	10	500
---------------	-----	----------------	----	----	-----

120 LB Steel Barb Tie

CTSB15NT120-L	15"	00076308925963	50	10	500
CTSB15NT120-D	15"	00076308925987	500	5	2500
CTSB18NT120-L	18"	00076308926014	50	10	500

UV-Resistant Black

18 LB Steel Barb Tie

CTSB4BK18-C	4"	00076308925796	100	10	1000
CTSB8BK18-C	8"	00076308925833	100	10	1000

40 LB Steel Barb Tie

CTSB6BK40-C	6"	00076308925819	100	10	1000
-------------	----	----------------	-----	----	------

50 LB Steel Barb Tie

CTSB8BK50-C	8"	00076308925857	100	10	1000
CTSB8BK50-M	8"	00076308925871	1000	5	5000
CTSB11BK50-C	11"	00076308925895	100	10	1000
CTSB11BK50-M	11"	00076308925918	1000	5	5000
CTSB15BK50-C	15"	00076308925932	100	5	500
CTSB15BK50-M	15"	00076308925956	1000	5	5000

110 LB Steel Barb Tie

CTSB28BK110-L	28"	00076308926021	50	10	500
---------------	-----	----------------	----	----	-----

120 LB Steel Barb Tie

CTSB15BK120-L	15"	00076308925970	50	10	500
CTSB15BK120-D	15"	00076308925994	500	5	2500
CTSB18BK120-L	18"	00076308926007	50	10	500

Sample Pack

Steel Barb Tie Sample Pack

CTSB-SAMPLE	—	00076308926199	35	20	700
-------------	---	----------------	----	----	-----

Important Notice: Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. 3M's product warranty is stated in its Product Literature available upon request. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, **3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electrical Markets Division
Austin, TX
Web: www.3M.com/electrical

3M is a trademark of
3M Company.
© 3M 2019 HB14740
All rights reserved.
80-6016-0890-6