




HIGH PERFORMANCE INTERCONNECT (HPI) CONNECTORS

QUICK REFERENCE GUIDE

TE Connectivity's (TE) wire-to-board High Performance Interconnect (HPI) connector system is available in 1.0mm, 1.25mm, 1.5mm, 2.0mm, and 2.5mm centerline pitches. HPI products can be used where a signal or low power needs to be routed through a device. This wire-to-board connector system is available in vertical and horizontal (right angle) mounting orientations for design versatility. Square peg technology enables product compatibility with industry standard products.

FEATURES

- 1.0mm – 2.5mm centerline
- Vertical and horizontal PCB mount
- Through hole (DIP) & surface mount termination (SMT)
- Polarized
- Partially and fully shrouded
- Square termination posts
- Locking and gold plating options available
- Rated up to 3A

BENEFITS

- Provides design flexibility
- Cost effective
- Ensures proper compatibility of both the header and the housing
- Prevents stubbing contacts
- Enables interchangeability with industry standard designs


APPLICATIONS

- Business and retail equipment
- Consumer devices
- Industrial
- Automotive
- Medical
- Appliances


COMPONENTS: HOW TO READ THE PRODUCT MATRIX DIMENSIONS

Understanding the HPI connector's PCB footprint will help you quickly determine if the HPI product line is the correct wire-to-board solution to meet your design objectives. The product matrix helps you understand the PCB footprint. Note that only PCB headers have a PCB footprint, but the mating housing will also consume valuable space within a device, which is why we highlight both products' dimensions. The length (X) dimension is different for each position size, however, both the height (Y) and width (Z) are constant dimensions for each base PN. All the length dimensions are listed in the product selector table for a two position connector. The length of the connector can be calculated using the information in the charts. For example, If you decide that PN 1734595 is the connector that you need, then a two position connector's length is 4.3mm. However, if you need a three position connector, the length of the connector is 5.3mm, which is 4.3mm + 1.0mm. In this case, each additional position size requires an increase of 1.0mm in length. (Please refer to customer drawings for tolerances.)

HOUSING DIMENSIONS



HEADER DIMENSIONS



- 2 position length = 4.3mm
- 9 positions – 2 positions = 7 positions
- 7 positions * 1.0mm per pin increase = 7.0mm
- 9 position length = 4.3mm + 7.0mm = 11.3mm



READING DIMENSIONS IN THE PRODUCT MATRIX

PIN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)
1734595	Header	28-32	SMT	Vertical	2 to 15	4.3 + 1.0 Per Pin Increase	4.30	5.10

Connector Dimensions (mm)

PRODUCT OVERVIEW, RATINGS, AND SPECIFICATIONS

In order to better understand the product capabilities and limitations, it is advised that you refer to TE's specifications. The following table is intended to be used with the product selector matrix. The product matrix has a column on the far right that indicates the Spec Group, which aligns with the first column on the left in the graph below.

Spec Group	Centerline (mm)	PCB Termination Style	Product Specification	Application Specification	Qualification Reports	Rated Current Amps (Max.)	Rated Voltage (Max.)	Rated Voltage (Volts)	Operating Temp.
A	1.00	SMT	108-57264	114-57020	501-57283	1.00	50	AC/DC	-55 to 105°C
B			108-115169	114-115031	501-115186	1.00	50	AC	-40 to 85°C
B2			108-161430	108-161430	501-161458	1.00	50	AC	-25 to 85°C
C	1.25	SMT & DIP	108-57225	114-57016	501-57229	1.00	100	AC	-40 to 85°C
D			108-57499	114-57016	501-57573	1.00	125	AC/DC	-25 to 85°C
E			108-57273	114-57016	501-57299	1.00	100	AC	-40 to 85°C
F			108-115184	501-115199	501-115199	1.00	50	AC	-40 to 105°C
G	1.50	SMT	108-57631	114-57018	501-57736	3.00	250	AC	-55 to 105°C
H			108-115183	501-115198	501-115198	3.00	50	AC	-40 to 105°C
H2			108-115188	108-115188	501-115203	3.00	50	AC	-40 to 105°C
I	2.00	SMT & DIP	108-51087	114-57011	501-51084	3.00	250	AC/DC	-25 to 85°C
J			108-57100	114-57011	501-57058	3.00	250	AC/DC	-25 to 85°C
K			108-57499	114-57011	501-57573	1.00	125	AC/DC	-25 to 85°C
L			108-57217	114-57013	501-57218	3.00	100	DC	-25 to 85°C
M	2.50	SMT & DIP	108-57099	114-57004	501-57057	3.00	250	AC/DC	-25 to 85°C
N			108-57175	114-57012	501-57195	3.00	250	AC/DC	-40 to 105°C

Connector Dimensions (mm)



PRODUCT MATRIX: HOW TO SELECT AN HPI CONNECTOR PART NUMBER

The charts on this page highlight the relationship between the key product features, including AWG, PCB termination style, mount angle, position range, and dimensions to the product base number. Once you determine the correct base number, please refer to TE's website.

1.00MM HPI CONNECTORS

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
1734597-1	Contact	28 - 32	N/A	N/A	N/A	N/A	N/A	N/A	1470364	A
1470364	Housing	28 - 32	N/A	N/A	2 to 15	5.0 + 1.0 Per Pin Increase	2.80	5.00	1734595; 1734709	A
1734595	Header	28 - 32	SMT	Vertical	2 to 15	4.3 + 1.0 Per Pin Increase	4.30	5.10	1470364	A
1734709	Header	28 - 32	SMT	Right Angle	2 to 15	4.3 + 1.0 Per Pin Increase	2.90	4.95	1470364	A
2367199	Contact (Locking)	28 - 32	N/A	N/A	N/A	N/A	N/A	N/A	2367198	B
2367198	Housing (Locking)	28 - 32	N/A	N/A	3 to 15	6.0 + 1.0 Per Pin Increase	2.8	5	2367196; 2367197	B
2367196	Header (Locking)	28 - 32	SMT	Right Angle	3 to 15	5.0 + 1.0 Per Pin Increase	2.9	4.3	2367198	B
2367197	Header (Locking)	28 - 32	SMT	Vertical	3 to 15	5.0 + 1.0 Per Pin Increase	4.3	2.9	2367198	B

Connector Dimensions (mm)

The hand tool for terminal PN 1734597-1 is 2119536-1.

1.00MM HPI CONNECTORS - DUAL ROW

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
2484144	Contact	28 - 32	N/A	N/A	N/A	N/A	N/A	N/A	x-2484142-x	B2
2484142	Housing* (Locking)	28 - 32	N/A	N/A	12 - 50	11.35 + 1.00 Per Pin Increase	5.8	4.9	x-2484140-x	B2
2484140	Header* (Locking)	28 - 32	SMT	Vertical	12 - 50	9.1 + 1.00 Per Pin Increase	4.67	6.7	x-248142-x	B2

Connector Dimensions (mm)

1.25MM HPI CONNECTORS

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
1734193-1	Contact	28 - 32	N/A	N/A	N/A	N/A	N/A	N/A	440146-x	C
440146	Housing	28 - 32	N/A	N/A	2 to 15	4.25 + 1.25 Per Pin Increase	3.15	3.95	1734260-x; 1734261-x; 1734829-x; 1734598-x	C
1734260	Header	28 - 32	SMT	Vertical	2 to 15	7.79 + 1.25 Per Pin Increase	4.75	4.25	440146-x	D
1734260	Header	28 - 32	SMT	Vertical	2 to 15	7.79 + 1.25 Per Pin Increase	4.75	4.25	440146-x	D
1734261	Header	28 - 32	SMT	Right Angle	2 to 15	7.79 + 1.25 Per Pin Increase	3.45	4.70	440146-x	E
1734829	Header	28 - 32	DIP	Right Angle	2 to 15	4.25 + 1.25 Per Pin Increase	3.20	4.70	440146-x	E
1734598	Header	28 - 32	DIP	Vertical	2 to 15	4.25 + 1.25 Per Pin Increase	4.70	3.20	440146-x	E
2390147	Contact (Locking)	26-30	N/A	N/A	N/A	N/A	N/A	N/A	2390144-x	F
2390144	Housing (Locking)	26-30	N/A	N/A	2 to 15	3.75 + 1.25 Per Pin Increase	4.15	5.70	2390138-x; 2390136-x	F
2390138	Header (Locking)	26-30	SMT	Vertical	2 to 15	5.75 + 1.25 Per Pin Increase	4.25	4.05	2390144-x	F
2390136	Header (Locking)	26-30	SMT	Right Angle	2 to 15	5.75 + 1.25 Per Pin Increase	4.25	4.05	2390144-x	F

Connector Dimensions (mm)

The hand tool for terminal PN 1734193-1 is 2119537-1.

1.50MM HPI CONNECTORS

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
1775442-1	Contact	24 - 30	N/A	N/A	N/A	N/A	N/A	N/A	1775441-x	E
1775441	Housing	24 - 30	N/A	N/A	2 to 15	4.25 + 1.50 Per Pin Increase	2.70	6.15	1775443-x; 1775444-x	E
1775443	Header	24 - 30	SMT	Vertical	2 to 15	4.50 + 1.50 Per Pin Increase	5.00	6.00	1775441-x	E
1775444	Header	24 - 30	SMT	Right angle	2 to 15	4.25 + 1.50 Per Pin Increase	4.45	7.00	1775441-x	G
2380403	Contact (Locking)	24 - 30	N/A	N/A	N/A	N/A	N/A	N/A	2380312-9	H
2380312	Housing (Locking)	24 - 30	N/A	N/A	2 to 15	4.10 + 1.50 Per Pin Increase	3.0	5.7	2380320-x; 2381626-x	H
2380320	Header (Locking)	24 - 30	SMT	Vertical	2 to 15	4.30 + 1.50 Per Pin Increase	4.45	5.75	2380312-x	H
2381626	Header (Locking)	24 - 30	SMT	Right Angle	2 to 15	5.90 + 1.50 Per Pin Increase	4.40	5.00	2380312-x	H

Connector Dimensions (mm)

The hand tool for terminal PN 1775442-1 is 2119538-1.

1.5MM HPI CONNECTORS - DUAL ROW

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (x)	Height (y)	Width (z)	Mating Base PN	Product Spec Group
2380403	Contact	24-30	N/A	N/A	N/A	N/A	N/A	N/A	x-2394528-x	H2
2394528	Housing* (Locking)	24-30	N/A	N/A	10-30	8.6 + 0.75 Per Pin Increase	6.7	5.2	x-2394520-x; x-2394521-x	H2
2394520	Header* (Locking)	24-30	SMT	Vertical	10-30	12.5 + 0.75 Per Pin Increase	5.2	6.8	x-2394528-x	H2
2394521	Header* (Locking)	24-30	SMT	Right Angle	10-30	10.8 + 0.75 Per Pin Increase	8.5	7.8	x-2394528-x	H2

Connector Dimensions (mm)

The hand tool for terminal PN 2380403 is 2119538-1.

2.00MM HPI CONNECTORS

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
1735801-1	Contact	24 - 30	N/A	N/A	N/A	N/A	N/A	N/A		
440129	Housing	24 - 30	N/A	N/A	2 to 16	4.7 + 2.00 Per Pin Increase	4.50	6.90	440054-x; 440055-x; 1775470-x; 1775469-x;	J
440054	Header	24 - 30	DIP	Vertical	2 to 16	6.0 + 2.00 Per Pin Increase	6.05	4.70	440129-x	J
440055	Header	24 - 30	DIP	Right Angle	2 to 16	6.0 + 2.00 Per Pin Increase	4.95	7.70	440129-x	J
1775470	Header	24 - 30	SMT	Vertical	2 to 16	7.4 + 2.00 Per Pin Increase	6.15	5.40	440129-x	J
1775469	Header	24 - 30	SMT	Right Angle	2 to 16	7.4 + 2.00 Per Pin Increase	5.50	7.60	440129-x	J
1734827	Header	24 - 30	SMT	Right Angle	2 to 15	8.0 + 2.00 Per Pin Increase	5.60	6.00	440129-x	H
1735447	Housing (Locking)	24 - 30	N/A	N/A	3 to 16	7.92 + 2.00 Per Pin Increase	6.55	9.40	1735446-x	G
1735446	Header (Locking)	24 - 30	DIP	Vertical	3 to 16	8.0 + 2.00 Per Pin Increase	6.07	5.20	1735447-x	G
1470106-1	Contact	22 - 28	N/A	N/A	N/A	N/A	N/A	N/A	1470107-x	J
1470107*	Housing	22 - 28	N/A	N/A	6 to 32	8.0 + 2.00 Per Pin Increase	5.10	7.40	1470109-x; 1470108-x	J
1470109*	Header	22 - 28	DIP	Vertical	6 to 32	8.0 + 2.00 Per Pin Increase	6.50	5.00	1470107-x	J
1470108*	Header	22 - 28	DIP	Right Angle	6 to 32	8.0 + 2.00 Per Pin Increase	5.00	9.50	1470107-x	J

* = Dual Row Connectors

Connector Dimensions (mm)

The hand tool for terminal PNs 440132-1 and 1735801-1 is 2119539-1.

2.50MM HPI CONNECTORS

Base PN	Product Type	AWG	PCB Termination Style	Mount Angle	Position Range	Length (X)	Height (Y)	Width (Z)	Mating Base PN	Product Spec. Group
KINKED PINS										
440134-1	Contact	22 - 28	N/A	N/A	N/A	N/A	N/A	N/A	440133-x	K
440133	Housing	22 - 28	N/A	N/A	2 to 15	7.1 + 2.50 Per Pin Increase	4.20	7.15	440052-x; 440053-x; 1775317-x; 1775316-x	K
440052	Header	22 - 28	DIP	Vertical	2 to 15	7.5 + 2.50 Per Pin Increase	6.00	3.80	440133-x	K
440053	Header	22 - 28	DIP	Right Angle	2 to 14	7.5 + 2.50 Per Pin Increase	4.20	8.20	440133-x	K
1775317	Header	22 - 28	SMT	Vertical	2 to 15	9.5 + 2.50 Per Pin Increase	6.40	4.80	440133-x	K
1775316	Header	22 - 28	SMT	Right Angle		8.8 + 2.50 Per Pin Increase	4.80	7.70	440133-x	K
STRAIGHT PINS										
1470223-1	Contact	22 - 28	N/A	N/A	N/A	N/A	N/A	N/A	1470222-x	L
1470222	Housing	22 - 28	N/A	N/A	2 to 15	7.4 + 2.50 Per Pin Increase	4.70	8.00	1470224-x	L
1470224	Header	22 - 28	DIP	Vertical	2 to 15	7.5 + 2.50 Per Pin Increase	5.90	4.90	1470222-x	L

Connector Dimensions (mm)

There are no hand tools available for these terminals.

APPLICATIONS



Business & Retail Equipment

- Copiers
- Printers
- Scanners
- Fax Machines
- Projectors
- Vending Machines
- ATMs



Industrial Industry

- Appliances
- Industrial Controls
- GPS
- Thermostats
- HVAC
- Lighting



Consumer Devices

- PCs
- Ultrabook Devices
- Game Consoles
- Set Top Boxes
- Stereo Equipment



Medical Industry

- Medical Monitors
- Imaging Systems
- Portable Stations
- Treatment Equipment


CABLE ASSEMBLIES

For convenience, a selection of double-ended cable assemblies is available. These cable assemblies are useful for prototyping or for small production runs. For additional sizes, lengths or connector styles, please reach out to the TE sales team or to customer care.


PN	Description	Length	Positions	Housing PN	Contact PN	Wire Gauge	Wire Temp Rating	Wire Voltage Rating	Wire Color
2405396-2	1mm 2P CABLE ASSEMBLY, 1470364-2	300 mm	2	1470364-2	1734597-1	28 AWG	105° C	30V	Orange
2405396-3	1mm 3P CABLE ASSEMBLY, 1470364-3	300 mm	3	1470364-3	1734597-1	28 AWG	105° C	30V	Orange
2405396-4	1mm 5P CABLE ASSEMBLY, 1470364-5	300 mm	5	1470364-5	1734597-1	28 AWG	105° C	30V	Orange
2405396-1	1mm 8P CABLE ASSEMBLY, 1470364-8	300 mm	8	1470364-8	1734597-1	28 AWG	105° C	30V	Orange
2405396-5	1mm 10P CABLE ASSEMBLY, 1-1470364-0	300 mm	10	1-1470364-0	1734597-1	28 AWG	105° C	30V	Orange
2405396-6	1mm 12P CABLE ASSEMBLY, 1-1470364-2	300 mm	12	1-1470364-2	1734597-1	28 AWG	105° C	30V	Orange
2405415-3	1mm Locking 3P CABLE ASSEMBLY, 2367198-3	300 mm	3	2367198-3	2367199-1	28 AWG	105° C	30V	Orange
2405415-4	1mm Locking 5P CABLE ASSEMBLY, 2367198-5	300 mm	5	2367198-5	2367199-1	28 AWG	105° C	30V	Orange
2405415-1	1mm Locking 8P CABLE ASSEMBLY, 2367198-8	300 mm	8	2367198-8	2367199-1	28 AWG	105° C	30V	Orange
2405415-5	1mm Locking 10P CABLE ASSEMBLY, 1-2367198-0	300 mm	10	1-2367198-0	2367199-1	28 AWG	105° C	30V	Orange
2405415-6	1mm Locking 12P CABLE ASSEMBLY, 1-2367198-2	300 mm	12	1-2367198-2	2367199-1	28 AWG	105° C	30V	Orange
2405416-2	1.25mm 2P CABLE ASSEMBLY, 440146-2	300 mm	2	440146-2	440147-2	28 AWG	80° C	300V	Orange
2405416-3	1.25mm 3P CABLE ASSEMBLY, 440146-3	300 mm	3	440146-3	440147-2	28 AWG	80° C	300V	Orange
2405416-4	1.25mm 5P CABLE ASSEMBLY, 440146-5	300 mm	5	440146-5	440147-2	28 AWG	80° C	300V	Orange
2405416-1	1.25mm 8P CABLE ASSEMBLY, 440146-8	300 mm	8	440146-8	1734193-1	28 AWG	80° C	300V	Orange
2405416-5	1.25mm 10P CABLE ASSEMBLY, 1-440146-0	300 mm	10	1-440146-0	440147-2	28 AWG	80° C	300V	Orange
2405416-6	1.25mm 12P CABLE ASSEMBLY, 1-440146-2	300 mm	12	1-440146-2	440147-2	28 AWG	80° C	300V	Orange
2405417-2	1.5mm 2P CABLE ASSEMBLY, 1775441-2	300 mm	2	1775441-2	1775442-1	28 AWG	80° C	300V	Orange
2405417-3	1.5mm 3P CABLE ASSEMBLY, 1775441-3	300 mm	3	1775441-3	1775442-1	28 AWG	80° C	300V	Orange
2405417-4	1.5mm 5P CABLE ASSEMBLY, 1775441-5	300 mm	5	1775441-5	1775442-1	28 AWG	80° C	300V	Orange
2405417-1	1.5mm 8P CABLE ASSEMBLY, 1775441-8	300 mm	8	1775441-8	1775442-1	28 AWG	80° C	300V	Orange
2405417-5	1.5mm 10P CABLE ASSEMBLY, 1-1775441-0	300 mm	10	1-1775441-0	1775442-1	28 AWG	80° C	300V	Orange
2405417-6	1.5mm 12P CABLE ASSEMBLY, 1-1775441-2	300 mm	12	1-1775441-2	1775442-1	28 AWG	80° C	300V	Orange
2405418-2	2mm 2P CABLE ASSEMBLY, 440129-2	300 mm	2	440129-2	1735801-1	26 AWG	80° C	300V	Orange
2405418-3	2mm 3P CABLE ASSEMBLY, 440129-3	300 mm	3	440129-3	1735801-1	26 AWG	80° C	300V	Orange
2405418-4	2mm 5P CABLE ASSEMBLY, 440129-5	300 mm	5	440129-5	1735801-1	26 AWG	80° C	300V	Orange
2405418-1	2mm 8P CABLE ASSEMBLY, 440129-8	300 mm	8	440129-8	1735801-1	26 AWG	80° C	300V	Orange
2405418-5	2mm 10P CABLE ASSEMBLY, 1-440129-0	300 mm	10	1-440129-0	1735801-1	26 AWG	80° C	300V	Orange
2405418-6	2mm 12P CABLE ASSEMBLY, 1-440129-2	300 mm	12	1-440129-2	1735801-1	26 AWG	80° C	300V	Orange
2405419-2	2.5mm 2P CABLE ASSEMBLY, 440133-2	300 mm	2	440133-2	440134-1	24 AWG	80° C	300V	Orange
2405419-3	2.5mm 3P CABLE ASSEMBLY, 440133-3	300 mm	3	440133-3	440134-1	24 AWG	80° C	300V	Orange
2405419-4	2.5mm 5P CABLE ASSEMBLY, 440133-5	300 mm	5	440133-5	440134-1	24 AWG	80° C	300V	Orange
2405419-1	2.5mm 8P CABLE ASSEMBLY, 440133-8	300 mm	8	440133-8	440134-1	24 AWG	80° C	300V	Orange
2405419-5	2.5mm 10P CABLE ASSEMBLY, 1-440133-0	300 mm	10	1-440133-0	440134-1	24 AWG	80° C	300V	Orange
2405419-6	2.5mm 12P CABLE ASSEMBLY, 1-440133-2	300 mm	12	1-440133-2	440134-1	24 AWG	80° C	300V	Orange

COMPONENTS: A COMPLETE SOLUTION


A typical crimp type wire-to-board interconnect solution requires four components. A raw discrete wire, which is stripped, and then a crimp type contact is crimped onto the wire. The contact and wire are then inserted into an unloaded receptacle housing, which is mated with a header that is terminated to a PCB either through hole (DIP) or SMT style.




Raw Discrete Wire (Stripped)



Crimp Contact



Receptacle Housing



PCB Header


HPI ATTRIBUTES

PCB MOUNT ORIENTATION

Depends on the direction that the housing mates with the PCB header.


Right Angle

The housing is mated parallel to the PCB.



Vertical

The housing is mated perpendicular to the PCB.




TERMINATION METHOD TO PCB

Depends on how the PCB header is applied to a PCB.


Through Hole (DIP)

Attached to PCB by inserting PCB traces into the pre-drilled holes in the PCB and then soldered on the bottom side of the board.




Surface Mount (SMT)

Attached to the PCB by soldering process where PCB traces are soldered to the top of a PCB.




SQUARE TERMINATION POSTS

This design is an industry standard that allows TE's products to be interchanged with other industry standard products.



Polarized

Ensures that PCB headers and cable side receptacle housings properly mate.



FREQUENTLY ASKED QUESTIONS

The charts on this page highlight the relationship between the key product features, including AWG, PCB termination style, mount angle, position range, and dimensions to the product base number. Once you determine the correct base number, please refer to TE's website.

Question 1

What gauge wire (AWG) will you be using?

Answer 1

TE's HPI product accepts 22-32 AWG discrete wire. Remember that the higher the AWG measurement number, the smaller the discrete wire. For example, 32 AWG is smaller than 22 AWG will likely have less current carrying capacity.

Question 2

Are you transferring signal or lower power throughout your device?

Answer 2

HPI products are simple interconnect solutions that can be used to transfer signal or lower power in multiple applications across many industries.

Question 3

Does your application have a fan, motor, switch, display, light or any other simple device?

Answer 3

HPI product may be the ideal solution to control these type of ancillary items.

Question 4

Does your application require a locking feature to strengthen the mating connection between the plug assembly and receptacle?

Answer 4

If your application requires a secure mating retention feature, TE's 1.0mm and 2.0mm HPI product line offers an external locking feature to improve the reliability of the interconnect system.

Question 5

What are the technical requirements of your application?

Answer 5

It is imperative that you ask your customer the current and voltage requirements of their application. Current, which is expressed in amps, is usually the driving factor when selecting a small pitch wire-to-board product. Other information that you should consider include operating temperature, PCB real estate, profile height limitations, material restrictions, etc.

Question 6

What tooling is available to apply TE's wire-to-board products?

Answer 6

TE's tooling divisions offers a wide range of hand tools, semi-automatic, and automatic tools. Please visit <https://www.te.com/usa-en/products/application-tooling.html> to determine the application tooling that meets your needs.

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE (logo) and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity plc. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2025 TE Connectivity. All Rights Reserved.

06-25