

Applications

The PXI platform offers not only high flexibility and fast test speed, but powerful software customization capabilities that make it the ideal platform for entering newly emerging application fields.



Effective Modernization for Automated Semiconductor Testing


Traditional ATE systems are designed for high-performance testing needs but can be costly due to unnecessary features in large package solutions. The Chroma 3300 system, integrating the ADLINK PXI chassis and controller allows easy reconfiguration for expanding test requirements and uses unified software, saving time and costs.

Customer Benefits

- 18-slot Gen3 PXIe chassis with various modular solutions enhances testing efficiency
- Intel® Core™ i7-7820EQ-based PXIe controller provides high performance computing
- User-friendly PXIe CRAFT platform accelerates testing, result transfers, and large-scale operations

Products

- PXES-2788 18-slot Gen3 PXIe chassis
- PXIe-3987 Intel® Core™ i7-7820EQ-based controller
- Chroma 3300 series PXI tester with power supply and relay drive control
- Chroma semiconductor grade CRAFT-PXIe-software



High-Efficient HIL Testing for Self-driving Controller

Self-driving controllers process sensor data (LiDARs, mmWave radars, cameras) for real-time tasks. Hardware-in-the-Loop (HIL) testing is cost efficient and quicker to develop. Traditional costly HIL setups face synchronization issues. PXI-based HIL systems provide high bandwidth, power, and efficient cooling for high-speed components and I/O ports.

Customer Benefits

- 18-slot PXIe Gen3 chassis provides high density, expandable functional testing
- 1170W of total power with 82W cooling capacity components and high I/O count testing
- 11th Gen Intel® Core™ i7 processor enables real-time system, ensuring low-latency response, simulation

Products

- PXES-2785 18-slot 24GB/s PXIe Gen3 chassis
- PXIe-3987 Intel® Core™ i7-7820EQ Gen3 PXIe Controller
- ADLINK data acquisition and communication modules



Head Office

ADLINK Technology, Inc.

No. 66, Huaya 1st Rd., Guishan Dist.,
Taoyuan City 333411, Taiwan
Tel : +886-3-216-5088
Fax: +886-3-328-5706

f l n i n s t w www.adlinktech.com

Worldwide Offices

Ampro ADLINK Technology, Inc.

6450 Via Del Oro, San Jose, CA 95119-1208, USA
Tel: +1-408-360-0200
Toll Free: +1-800-966-5200 (USA only)
Fax: +1-408-360-0222
Email: info@adlinktech.com

ADLINK Technology (China) Co., Ltd.

上海市浦东新区张江高科技园区芳春路300号 (201203)
300 Fang Chun Rd., Zhangjiang Hi-Tech Park
Pudong New Area, Shanghai, 201203 China
Tel: +86-21-5132-8988
Fax: +86-21-5192-3588
Email: market@adlinktech.com

ADLINK Technology Beijing

北京市海淀区上地东路1号盈创动力大厦E座801室
(100085)
Rm. 801, Power Creative E, No. 1 Shang Di East Rd.
Beijing, 100085 China
Tel: +86-10-5885-8666
Fax: +86-10-5885-8626
Email: market@adlinktech.com

ADLINK Technology Shenzhen

深圳市南山区科技园南区高新南七道数字技术园
A1栋2楼C区(518057)
2F, C Block, Bldg. A1, Cyber-Tech Zone, Gao Xin
Ave. Sec. 7 High-Tech Industrial Park S.,
Shenzhen, 518054 China
Tel: +86-755-2643-4858
Fax: +86-755-2644-6353
Email: market@adlinktech.com

ADLINK Technology Singapore Pte. Ltd.

84 Genting Lane #07-02A, Axcel Innovation
Centre, Singapore 349584
Tel: +65-6844-2261
Fax: +65-6844-2263
Email: singapore@adlinktech.com

ADLINK Technology Singapore Pte Ltd. (Indian Liaison Office)

#50-56, First Floor, Spearhead Towers
Margosa Main Road (between 16th/17th Cross)
Malleswaram, Bangalore - 560 055, India
Tel: +91-80-42246107, +91-80-23464606
Fax: +91-80-23464606
Email: india@adlinktech.com

ADLINK Technology Japan Corporation

〒101-0045 東京都千代田区神田鍛冶町3-7-4
ユニゾ神田鍛冶町三丁目ビル4F
Unizo Kanda Kaji-cho 3 Chome Bldg. 4F,
3-7-4 Kanda Kajicho, Chiyoda-ku,
Tokyo 101-0045, Japan
Tel: +81-3-4455-3722
Fax: +81-3-5209-6013
Email: japan@adlinktech.com

ADLINK Technology Korea Ltd.

경기도 용인시 수지구 신수로 767 A동 1503호
(동천동, 분당수지유타워) (주) 16827
A-1503, U-TOWER, 767 Sinsu-ro, Suji-gu,
Yongin-si, Gyeonggi-do, Republic of Korea, 16827
Toll Free: +82-80-800-0585
Tel: +82-31-786-0585
Fax: +82-31-786-0583
Email: korea@adlinktech.com

ADLINK Technology, Inc. (Israel Liaison Office)

MIXER Herzliya (Building B, 9 Floor)
3 Arik Einstein st., Zip code 4610301
Herzliya, Israel, P.O.Box - 351
Tel: +972-54-632-5251
Fax: +972-77-208-0230
Email: israel@adlinktech.com

ADLINK Technology GmbH

Hans-Thoma-Straße 11
D-68163 Mannheim, Germany
Tel: +49 621 43214-0
Fax: +49 621 43214-30
Email: germany@adlinktech.com

Ulrichsbergerstraße 17
D-94469 Deggendorf, Germany
Tel: +49 991 290 94-10
Fax: +49 991 290 94-29
Email: germany@adlinktech.com

ADLINK Technology, Inc. (French Liaison Office)


Bâtiment Thalès - Parc des Algorithmes,
Route de l'Orme des Merisiers,
91190 SAINT AUBIN, France
Tel: +33 (0) 1 60 12 35 66
Fax: +33 (0) 1 60 12 35 68
Email: france@adlinktech.com

ADLINK Technology, Inc. (UK Liaison Office)

First Floor West Exeter House,
Chichester fields Business Park Tangmere,
West Sussex, PO20 2FU, United Kingdom
Tel: +44-1243-859677
Email: uk@adlinktech.com

The Best Balance of Functionality,
Performance, and Cost

Future-ready
PXI Platforms and
Modules



Learn More
PXI Solutions

All products and company names listed are trademarks or trade names of their respective companies. ©2024 ADLINK Technology, Inc. All Rights Reserved. All pricing and specifications are subject to change without further notice.





Gen3 PXI Solution Optimizes Performance and Cost

The Gen3 PXI platform sets the standard in modular automated test equipment. Its modules, chassis, and controllers offer interoperability. Manufacturers and labs benefit from off-the-shelf, plug-and-play PXI modules for custom testing. The PXI's open architecture provides key features for automated testing including flexibility, affordability, and high performance.



Interoperability

Compatible with standard modular instruments in the T&M industry



High Performance


Based on the latest technology, incorporating powerful multicore processors, FPGAs, and more to speed up time to market



Scalable

PXI architecture synchronizes measurements across modules/chassis for adaptive system expansion

Future-ready PXI Gen3 Platform Highlights



Empower High-Efficiency Testing in EV and LED Manufacturing

Electric Vehicle Battery Testing Solution

PXES-2788
18/21-Slot High-Power, High-Cooling PXIe Chassis

PXIe-3988
11th Gen Intel Xeon-based PXIe Controller

Chroma 52400 Series
2-ch, High Precision PXIe SMU

- Up to 1170W high power and 82W cooling capacity enables high density testing
- Wide range 200nA to 200mA current, 25V to 4mV source and measurement for high flexibility
- Low-noise output for accurate leakage current measurement

Mini/Micro LED Testing Solution

PXES-2785
18-Slot 24GB/s PXIe Chassis

PXIe-3987-TL
11th Gen Intel Core-based PXIe Controller

PXIe-9908
8-ch, Precision PXIe SMU

- 136-ch max high-density enables high-throughput testing
- High accuracy 100nA to 100mA current source and measurement
- Up to 100V voltage measurement range for reverse breakdown voltage (VR) testing

PXI Express Chassis

Gen3

PXES-2788
18/21-slot PXIe Gen3 Chassis with High Power and High Cooling capacity

Gen3

PXES-2785
18-slot 24GB/s PXIe Gen3 chassis

Gen2

PXES-2780/2590/2301
18/9/6-slot 8GB/s PXIe Gen2 Chassis

Thunderbolt

PXES-2314T
Compact 4-slot Thunderbolt™ 3 PXIe Gen3 Chassis

PXI Express Embedded Controller

Gen3

PXIe-39X7-TL/3988-TL
11th Gen Intel Core i7/i5/i3, Xeon-based PXIe Controller

PXIe Remote

PCle-PXIe-8640
PCle to PXIe Remote Controller PCIe Gen3, 8GB/s

PXI Express Modules

Source Measurement Unit

PXIe-9908
8-ch, ±10V~±90V ±100mA~±100nA, 100kS/s SMU , supports sink and source

52400 Series
2-ch, 18-bit. ±25V~±4mV, ±3.5A~±1uA, Low output noise, 100kS/s SMU

High Speed Digitizer

PXIe-9834/9852
4/2-ch, 16/14-bit, up to 200 MS/s PXIe digitizer with PLL

PXIe-9848/9848H
8-ch 14-bit 100 MS/s High-Speed PXIe Digitizer

Multi-function DAQ

PXI-2000 Series
4-ch, 14/16-bit, up to 2MS/s Simultaneous Sampling Multi-Function PXI Modules

PXI-2200 Series
96/64-ch, 12/16-bit, up to 3 MS/s Multi-Function PXI Modules