



The user experience requirements will become more demanding over the next couple of years. The resources of today's mobile broadband networks are becoming insufficient as operators offer broadband multimedia access anywhere to meet the increased demand. The MIMO Phantom MTRAx antenna are multi-protocol to support multiple applications with one antenna and are new members of Laird Connectivity's industry-leading Phantom series. They support high quality 2G, 3G, 4G, 5G, Cellular, ISM 868, ISM 900, SIGFOX, LoRaWAN, and the unlicensed 2.4 GHz band.

They are engineered for high reliability and they support 2x2 MIMO for better throughput. The MTRA61274Cx2 antennas are an excellent addition to new designs, or as a replacement for existing SISO phantom antennas.

FEATURES AND BENEFITS

- Covers 617-960 MHz and 1350-2700 MHz
- 2G, 3G, 4G, 5G, Cellular, WLAN, ISM, SIGFOX, LoRaWAN, unlicensed 2.4 GHz
- Omnidirectional high gain patterns
- Rugged IP67 for vehicle and fixed installations

APPLICATIONS

- IoT and M2M
- Smart metering and AMI
- Remote monitoring and control
- Industrial and energy
- Automation, robotics, and AI

ELECTRICAL SPECIFICATIONS

Antenna Model	MTRA61274Cx2									
Number of Ports	2									
Operating Frequency (MHz)	617-698	698-824	824-894	880-960	1350-1550	1690-1880	1850-1990	1910-2180	2300-2500	2500-2700
Peak Gain – Average (dBi)**	2.4	3.1	2.8	2.7	2.7	3.6	3.9	3.5	3.6	2.9
Peak Gain – Max (dBi)**	3.2	4.0	4.0	3.4	4.7	4.1	4.1	4.2	4.0	3.4
VSWR – Max*	2.5									
VSWR – Average*										
Port 1	1.4	1.8	1.9	1.9	1.5	1.3	1.4	1.8	1.8	1.9
Port 2	1.4	1.8	1.9	1.9	1.5	1.3	1.4	1.8	1.8	1.8
Port-to-Port Isolation	-8	-10	-10	-10	-15	-17	-18	-18	-18	-25
Nominal Impedance (Ohms)	50									
Polarization	Linear vertical									
Azimuth Beamwidth (°)	360, Omnidirectional									
Max Power - Ambient 25°C (W)	50									

*/** - Measured on a one-foot ground plane.

MECHANICAL SPECIFICATIONS

Dimensions – L x W x H – mm (inches)	130 x 84 x 95 (5.12 x 3.31 x 3.74)
Weight – g (oz.)	343 (12.1)
Radome/Baseplate Material	PC, UL94 V0 Rating, UV Stable

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature – °C (°F)	-30 to +70°C (-22 to +158°F)
Storage Temperature – °C (°F)	-40 to +85°C (-40 to +185°F)
Material Substance Compliance	RoHS
Ingress Protection	IP67 (when installed on a hard, flat surface)

CONFIGURATION


PART NUMBER	CABLE TYPE	CABLE LENGTH	CONNECTOR	COLOR
MTRA61274CB2-001	LMR195M	610 mm (24 in.)	SMA- male	Black
MTRA61274CW2-001	LMR195M	610 mm (24 in.)	SMA- male	White

Note: Specifications vary with different types of cable, different lengths of cables and connectors. Contact Laird for detailed specifications.

PACKAGING INFORMATION


PACKAGED DIMENSIONS	MASTER CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	20	480	600
Height - cm (in.)	30.0 (11.8)	135 (53.2)	165 (65.0)
Length - cm (in.)	52.5 (20.7)	105 (41.3)	105 (41.3)
Width - cm (in.)	26.5 (10.4)	79.5 (31.3)	79.5 (31.3)
Shipping Weight - kg (lbs.)	7.36 (16.2)	190 (419)	230 (507)

MECHANICAL DRAWING




RADIATION PATTERNS


633 MHz




725 MHz




849 MHz




925 MHz




1730 MHz




2140 MHz




1930 MHz



2300 MHz




2595 MHz




RADIATION PATTERNS

633 MHz




Elevation Plane 0° – Phi 0°


725 MHz




849 MHz




925 MHz




1730 MHz




2140 MHz




1930 MHz



2300 MHz




2595 MHz




RADIATION PATTERNS


633 MHz




725 MHz




849 MHz




925 MHz




1730 MHz




2140 MHz




1930 MHz



2300 MHz



2595 MHz



RoHS

Laird Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations Laird Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the Laird Connectivity product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

Any information furnished by Laird Connectivity and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Connectivity materials rests with the end user, since Laird Connectivity and its agents cannot be aware of all potential uses. Laird Connectivity makes no warranties as to the fitness, merchantability or suitability of any Laird Connectivity materials or products for any specific or general uses. Laird Connectivity shall not be liable for incidental or consequential damages of any kind. All Laird Connectivity products are sold pursuant to the Laird Connectivity Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2020 Laird Connectivity All Rights Reserved. Laird Connectivity, the Laird Connectivity logo, and other marks are trademarks or registered trademarks of Laird Connectivity or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Connectivity or any third party intellectual property rights.



sales@lairdconnect.com
support@lairdconnect.com
www.lairdconnect.com