

**SAISWZ-M-4A-6/8-M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

Tension-clamp connection delivers excellent functional security and reduced installation times. With this technology the conductor is plugged into the tension clamp without a wire-end ferrule (optionally with wire-end ferrule). The connection between the conductor and tension clamp is vibration-resistant and boasts long-term stability.

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">1344730000</a>
Type	SAISWZ-M-4A-6/8-M12
GTIN (EAN)	4050118146905
Qty.	1 pc(s).

**SAISWZ-M-4A-6/8-M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 63 g

**Technical data customisable plug-in connectors**

Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Coding	A-coded	Conductor cross-section, max.	0.5 mm <sup>2</sup>
Conductor cross-section, min.	0.14 mm <sup>2</sup>	Contact surface	Gold-plated
Gender of contact	Male	Housing main material	PA
Insulation strength	10 <sup>8</sup> Ω	Number of poles	4
Plugging cycles	≥ 100	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	250 V	Shield connection	Yes
Temperature range of housing	-40 ... +85 °C	Threaded ring material	Diecast zinc
Type of connection	Tension-clamp connection		

**General Info**

Number of poles	4	Connection 1	M12
Connection 2	Tension-clamp	Housing main material	PA
Connection thread	M12	Contact surface	Gold-plated
Protection degree	IP67	Plugging cycles	≥ 100

**Classifications**

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 9.0	27-44-01-02
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-02
ECLASS 11.0	27-44-01-02	ECLASS 12.0	27-44-01-16
ECLASS 13.0	27-44-01-02	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

**Approvals**

Approvals



Approvals MAMID [https://mdcop.weidmueller.com/mediadelivery/rendition/900\\_319222/-T1z1mm-S800/](https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/) [https://mdcop.weidmueller.com/mediadelivery/rendition/900\\_319260/-T1z1mm-S800/](https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/)

ROHS Conform

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

**SAISWZ-M-4A-6/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Engineering Data	<a href="#">CAD data – STEP</a> <a href="#">CAD data – DWG</a> <a href="#">CAD data – DXF</a>
User Documentation	<a href="#">Manual</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>

---

**Data sheet**

**SAISWZ-M-4A-6/8-M12**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Pole scheme**

