

**IE-C5ED8UG0010A40A40-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**General ordering data**

Version	Dragline cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 1 m
Order No.	<a href="#">1345030010</a>
Type	IE-C5ED8UG0010A40A40-E
GTIN (EAN)	4050118149753
Qty.	1 pc(s).

Creation date June 16, 2025 11:19:42 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

## IE-C5ED8UG0010A40A40-E

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Length	1 m	Length (inches)	39.37 inch
Net weight	71 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Installation temperature	-40 °C...80 °C		

## Cable specific standards

Impervious to smoke	According to IEC 61034-2	Standard, assembly	UL-Style 20963 (80°C/30V)
Standard, insulating material	DIN EN 50290-2-25 (HD 624.5)	Standard, shielding material	DIN EN 13602 Cu-ETP-A..B
Standard, wire material	DIN EN 13602 Cu-ETP-A		

## Cable structure

Arrangement of wire cores	Twisted pair	Colour sequence or wires - wire pairs	white/blue - blue, white/ orange - orange, white/ green - green, white/ brown - brown
Complete shielding	Plastic foil, Aluminium foil, Shielding braid made from copper wiring	Cross-section	4*2*AWG 26/7 - 4*2*0.128 mm <sup>2</sup>
Filler	As central element, Be- tween the individual wire pairs	Insulation cross-section	0.95 mm
Material sheath	PUR	Overlap of shielding braid	90 %
Sheath diameter, max.	6.8 mm	Sheath diameter, min.	6.5 mm
Sheathing colour	green (RAL 6018)	Sheathing material thickness	0.85 mm
Shielding	SF/UTP	Shielding braid thickness	0.1 mm
Standard designations	LI9Y(ST)C 11Y 4X2X0.14 VZN GN, SF/UTP	Strands	7
Wire core insulation thickness	0.23 mm	Wire material	Stranded tin-plated copper wire

## Electrical properties of cable

Capacity at 800 Hz	50 nF/km	Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)
Characteristic impedance	100 ± 15 Ω at 1-100 MHz	Delay skew	40 ns/100m
Loop resistance	290 Ω/km	Operating voltage (UL rating)	30 V
Operating voltage, UL	30 V	Resistance differential	2 %
Signal propagation time	5.55 ns/m	Speed	180 m/min
Test voltage: wire-wire-shield	700 V <sub>rms</sub> , 50 Hz, 1 min	Transfer impedance	100 mΩ/m at 10 MHz

## IE-C5ED8UG0010A40A40-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Mechanical and material properties of cable

Abrasion resistance	very good	Acceleration	5 m/s <sup>2</sup>
Fire propagation	No	Halogen	halogen-free, according to IEC 60754-2
Impervious to smoke	According to IEC 61034-2	Min. bending radius, repetitive	60 mm
Pulling force	≤ 100 N	Resistance to oils	in accordance with IEC 60811-2-1
Resistance to spread of flame	in accordance with IEC 60332-1	Silicone-free	Yes
Speed	180 m/min	Torsion resistance	30 °/m
UV-resistant	Yes		

## Plug

Plug left	RJ45, IP20, male contact, straight, Plastic, shielded	Plug right	RJ45, IP20, male contact, straight, Plastic, shielded
-----------	---	------------	---

## Plug, left

Plug left	RJ45, IP20, male contact, straight, Plastic, shielded
-----------	---

## Plug, right

Plug right	RJ45, IP20, male contact, straight, Plastic, shielded
------------	---

## Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Approvals

Approvals



Approvals MAMID [https://mdcop.weidmueller.com/mediadelivery/rendition/900\\_319222/-T1z1mm-S800/](https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/) [https://mdcop.weidmueller.com/mediadelivery/rendition/900\\_319260/-T1z1mm-S800/](https://mdcop.weidmueller.com/mediadelivery/rendition/900_319260/-T1z1mm-S800/)

ROHS Conform

**IE-C5ED8UG0010A40A40-E****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Technical data****Downloads**

---

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a>

---