

C300-36B-F-2S-M25-15M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-wired cables allow connecting the Honeywell C300 IOTAs (Input Output Terminal Assemblies) and the Weidmüller FTAs (Field Terminal Assemblies) in a manner that is quick, simple and error free.

The cables may be delivered with single or dual connectors, or even with free ends and end ferrules.

The hood makes it easier to handle and it offers a robust connection with the IOTA. It also allows using cables of different gauge sizes and lengths of up to 50m.

General ordering data

| | |
|------------|---|
| Version | Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm ² |
| Order No. | 1349370150 |
| Type | C300-36B-F-2S-M25-15M |
| GTIN (EAN) | 4032248190607 |
| Qty. | 1 pc(s). |

C300-36B-F-2S-M25-15M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|---------|
| Net weight | 6,587 g |
|------------|---------|

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

General Data

| | | | |
|--------------------|---|-----------------------|---|
| Cable | Cable LiYCY | Cable length | 15 m |
| Connector PLC side | H0.25/10 (FERRULES 0.25mm ²) | Interface connector | SP-BLZP 5.08 32P with clamshell, WEIDMUELLER BLT 5.08HC/04/180F |
| Material | PVC | Number of poles, min. | 36-pole |
| Outer diameter | 11,85 ± 1 mm | Suitable for | Digital signals |
| Wire cross-section | 0.25 mm ² | | |

Electrical Data

| | | | |
|--|-----------|-----------------------|-----------------------|
| Capacity wire / shield | 300 pF/m | Capacity wire / wires | 300 pF/m |
| High voltage test | 1 KV/1s | Operating voltage | ≤ 250 V DC ≤ 250 V AC |
| Permissible current strength per path, max. | 1 A | Rated voltage | ≤ 250 Vdc ≤ 250 Vac |
| Resistance | ≤ 80 mΩ/m | Total current, max. | 3 A |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 9.0 | 27-24-22-20 |
| ECLASS 9.1 | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |
| ECLASS 13.0 | 27-24-22-20 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Environmental Product Compliance

| | |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | No SVHC above 0.1 wt% |

Downloads

| | |
|-----------------------------|---|
| Product Change Notification | Product modification for PAC-NAI, PAC-HONEYWELL and C300 Pre-Assembled Cables |
| User Documentation | Colours chart |
| Catalogues | Catalogues in PDF-format |