

**AP DK4Q****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                                                                                        |
|------------|----------------------------------------------------------------------------------------|
| Version    | End plate for terminals, beige, Height: 54 mm, Width: 1.5 mm, V-2, PA 66, Snap-on: Yes |
| Order No.  | <a href="#">1397160000</a>                                                             |
| Type       | AP DK4Q                                                                                |
| GTIN (EAN) | 4008190125899                                                                          |
| Qty.       | 20 pc(s).                                                                              |

## AP DK4Q

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 43.5 mm | Depth (inches)  | 1.713 inch |
| Height     | 54 mm   | Height (inches) | 2.126 inch |
| Width      | 1.5 mm  | Width (inches)  | 0.059 inch |
| Net weight | 2.8 g   |                 |            |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 100 °C        |

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | PA 66 | Colour | beige |
| UL 94 flammability rating | V-2   |        |       |

## System specifications

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

## Additional technical data

|                     |                 |         |     |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 9.1  | 27-14-11-33 |
| ECLASS 10.0 | 27-14-11-33 | ECLASS 11.0 | 27-14-11-33 |
| ECLASS 12.0 | 27-14-11-33 | ECLASS 13.0 | 27-25-03-01 |
| ECLASS 14.0 | 27-25-03-01 | ECLASS 15.0 | 27-25-03-01 |

Cradle to gate 0.027 kg CO<sub>2</sub>eq.

## Environmental Product Compliance

|                          |                                               |
|--------------------------|-----------------------------------------------|
| RoHS Compliance Status   | Compliant without exemption                   |
| REACH SVHC               | No SVHC above 0.1 wt%                         |
| Product Carbon Footprint | de.myview.objectmodel.impl.BlockImpl@3cf10703 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                    |                                                 |
|--------------------|-------------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>                 |
| User Documentation | <a href="#">StorageConditionsTerminalBlocks</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>        |