

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME
CB TEST CERTIFICATE

Product

AC/DC switch mode power supply

Name and address of the applicant

VOX POWER LTD
Unit 2
Redcow Interchange Estate Dublin, 22 Ireland

Name and address of the manufacturer

VOX POWER LTD
Unit 2
Redcow Interchange Estate Dublin, 22 Ireland

Name and address of the factory

Panyu Trio Microtronics Co Ltd
SHIJI INDUSTRIAL ESTATE
DONGYONG
NANSHA GUANGZHOU, Guangdong, 511453 China

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

Input: 100 - 240 Vac, 50-60 Hz, 3A
[Additional Information on page 2](#)

Trademark / Brand (if any)

VOX-POWER

Customer's Testing Facility (CTF) Stage used

VCCS300M-aaaa-bbb
[Additional Information on page 2](#)

Model / Type Ref.

The risk management requirements of the standard were not addressed
National Differences: CA, US
[Additional Information on page 2](#)

Additional information (if necessary may also be reported on page 2)

IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005/AMD2:2020

A sample of the product was tested and found to be in conformity with

E316486-D1001-2/A0/C0-CB issued on 2023-09-19

As shown in the Test Report Ref. No. which forms part of this Certificate



UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
 UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
 UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
 UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-09-20

Signature:
Thomas Wilson

Factory(ies):

Trio-Tronics (Thailand) Ltd
7/295 Mu. 6
Map Yang Phon Sub-District Pluak Daeng District, Rayong Province,
Thailand

Additional Model Detail(s):

VCCS300M-aaaa-bbb, - aaaa denotes the output voltage and may be any value from 12 to 58 (including decimals to one significant digit)
- bbb may be blank or alphanumeric characters (non-safety related)

Additional Ratings:

Output: 12Vdc to 58Vdc (depends on model), max. 300 W For mains and thermal deratings please see Additional Information section

Additional information (if necessary)

- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Dernko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-09-20

Signature:



Thomas Wilson