

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME  
**CB TEST CERTIFICATE**

Product

Switch Mode Power Supply

Name and address of the applicant

VOX POWER LTD  
Unit 2  
Redcow Interchange Estate Dublin 22  
Ireland

Name and address of the manufacturer

VOX POWER LTD  
Unit 2  
Redcow Interchange Estate Dublin 22  
Ireland

Name and address of the factory

Panyu Trio Microtronics Co Ltd  
SHIJI INDUSTRIAL ESTATE  
DONGYONG  
NANSHA GUANGZHOU, GUANGDONG, 511453  
China

*Note: When more than one factory, please report on page 2*

[Additional Information on page 2](#)

Input rating: 100-240 V ac, 7 A, 50-60 Hz  
[Additional Information on page 2](#)



Customer's Testing Facility (CTF) Stage used

VCCM600S-abcd-zzzz  
[Additional Information on page 2](#)

Model / Type Ref.

**Additionally evaluated to:** EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020  
[Additional Information on page 2](#)

Additional information (if necessary may also be reported on page 2)

IEC 62368-1:2018

A sample of the product was tested and found to be in conformity with

E316486-A6007-CB-1 issued on 2022-11-30

As shown in the Test Report Ref. No. which forms part of this Certificate

This CB Test Certificate is issued by the National Certification Body



UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA  
 UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK  
 UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN  
 UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2022-11-30

Signature:  
Jan-Erik Storgaard

**Factory(ies):**

Trio-Tronics (Thailand) Ltd  
7/295 Mu. 6  
Map Yang Phon Sub-District Pluak Daeng District, Rayong Province,  
Thailand

**Additional Model Detail(s):**

VCCM600S-abcd-zzzz, where abcd is optional and denotes respectively slot 1, slot 2, slot 3, slot 4 and each may be as follows:  
0, A, B, C, or D. zzzz may be blank or alphanumeric characters.

Output modules:  
OPA, OPB, OPC, OPD

**Additional Ratings:**

Maximum output power is 600 W.

Individual outputs rated according to modules fitted.

Output modules output ratings (optional):

OPA = 1.5 - 7.5 V dc, 25 A, 125 W

OPB = 4.5 - 15 V dc, 15 A, 150 W

OPC = 9 - 30 V dc, 7.5 A, 150 W

OPD = 18 - 58 V dc, 3.75 A, 150 W

All output modules current and power ratings are the maximum allowable.

**Additional information (if necessary)**

- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2022-11-30

Signature:



Jan-Erik Storgaard