

KSPMH M32 SSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration**IECEx**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSPMH (Klippon blanking plug, type MH), Blanking plug, straight, M 32, 16 mm, Stainless steel 1.4404 (316L)
Order No.	1477890000
Type	KSPMH M32 SSC
GTIN (EAN)	4050118285901
Qty.	10 pc(s).

KSPMH M32 SSC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	21.5 mm	Height (inches)	0.846 inch
Length	21 mm	Length (inches)	0.827 inch
Diameter	32 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	15 mm	Net weight	142.9 g

Temperatures

Operating temperature	-60 °C...200 °C
-----------------------	-----------------

Certificate numbers cable gland

Approval conditions	ATEX, IECEX	Certificate no. cable gland (ATEX)	SIRA 09ATEX1320X or CML 19ATEX1089X
Certificate no. cable gland (IECEX)	IECEX SIR 09.0131X or IE- CEX CML 19.0022X	Identification	Ex d IIC Gb, Ex e IIC Gb, Ex tb IIIC Db

KSPMH M32 SSC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

General information

Diameter of sealing ring	32 mm	External thread	M 32
Halogen	halogen-free	Impact resistance	7 J ATEX version
Length of thread	16 mm	Material	Stainless steel 1.4404 (316L)
Note: protection class	• All metric sealing plugs have a thread pitch of 1.5 mm. • In Ex nR applications, the KSPMH must be fitted with a further seal. • To obtain the specified IP rating, the through hole must comply with the regulations of EN 50262 Table 1 and it should be possible to secure the sealing plug in a suitable manner. • Operating instructions are enclosed with each sealing plug; these must be read prior to installation. The sealing plugs must be installed according to the specifications in the operating instructions. • On installation of the KSPMH, the minimum number of engaged thread turns in line with the standard EN/IEC 60079-1, Section 5.3, must be observed. • With NEC / CEC applications, it must be ensured that the inner thread of the connection device into which the sealing plugs are screwed reveals at least 8 fully engaged thread turns. • If KSPMH sealing plugs are inserted into non-metallic Ex e connection devices, they must be connected to the system's earth circuit.		
O.D.	37.5 mm	O-Ring	Silicone
Operating temperature range, min.	-60 °C	Operating temperature range, max.	200 °C
Protection degree	IP66, IP68 (100 m / 168 h)	Protection class (UL)	Type 4X
Standards	EN 60079-31, EN 60079-0, EN 60079-1, EN 60079-7	Silicone	Yes
Water depth	100 m	Tightening torque	10 Nm

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05
ECLASS 13.0	27-14-08-05	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Creation date June 12, 2025 12:44:30 PM CEST

Catalogue status 07.06.2025 / We reserve the right to make technical changes.

KSPMH M32 SSC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	