


**SL 3.50/08/90G 3.2SN OR BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Pin headers for wave soldering in 3.50 mm pitch

- Plugging direction is parallel (90°), straight 180° or angled (135°) to the PCB
- Housing variant: screw flange (F)
- Packed in a cardboard box (BX)
- Pin header can be coded

**General ordering data**

|              |                                                                                                                                                              |
|--------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, closed side, THT solder connection, 3.50 mm, Number of poles: 8, 90°, Solder pin length (l): 3.2 mm, tinned, orange, Box |
| Order No.    | <a href="#">1605130000</a>                                                                                                                                   |
| Type         | SL 3.50/08/90G 3.2SN OR BX                                                                                                                                   |
| GTIN (EAN)   | 4008190172022                                                                                                                                                |
| Qty.         | 50 pc(s).                                                                                                                                                    |
| Product data | IEC: 320 V / 17 A<br>UL: 300 V / 10 A                                                                                                                        |
| Packaging    | Box                                                                                                                                                          |

Creation date June 13, 2025 9:18:05 PM CEST

## SL 3.50/08/90G 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|                          |            |                 |            |
|--------------------------|------------|-----------------|------------|
| Depth                    | 11.1 mm    | Depth (inches)  | 0.437 inch |
| Height                   | 10.7 mm    | Height (inches) | 0.421 inch |
| Height of lowest version | 7.5 mm     | Width           | 29.4 mm    |
| Width (inches)           | 1.157 inch | Net weight      | 2.11 g     |

## System specifications

|                                              |                                                  |                                            |                              |
|----------------------------------------------|--------------------------------------------------|--------------------------------------------|------------------------------|
| Product family                               | OMNIMATE Signal - series BL/SL 3.50              | Type of connection                         | Board connection             |
| Mounting onto the PCB                        | THT solder connection                            | Pitch in mm (P)                            | 3.5 mm                       |
| Pitch in inches (P)                          | 0.138 "                                          | Outgoing elbow                             | 90°                          |
| Number of poles                              | 8                                                | Number of solder pins per pole             | 1                            |
| Solder pin length (l)                        | 3.2 mm                                           | Solder pin length tolerance                | +0.1 / -0.3 mm               |
| Solder pin dimensions                        | d = 1.2 mm, Octagonal                            | Solder pin dimensions = d tolerance        | 0 / -0.03 mm                 |
| Solder eyelet hole diameter (D)              | 1.4 mm                                           | Solder eyelet hole diameter tolerance (D)+ | 0.1 mm                       |
| L1 in mm                                     | 24.5 mm                                          | L1 in inches                               | 0.965 "                      |
| Number of rows                               | 1                                                | Pin series quantity                        | 1                            |
| Touch-safe protection acc. to DIN VDE 57 106 | finger-safe plugged/ back-of-hand-safe unplugged | Touch-safe protection acc. to DIN VDE 0470 | IP20 plugged/ IP10 unplugged |
| Volume resistance                            | 6.00 mΩ                                          | Can be coded                               | Yes                          |
| Plugging force/pole, max.                    | 10 N                                             | Pulling force/pole, max.                   | 10 N                         |

## Material data

|                                       |                                                |                                       |                                  |
|---------------------------------------|------------------------------------------------|---------------------------------------|----------------------------------|
| Insulating material                   | PBT                                            | Colour                                | orange                           |
| Colour chart (similar)                | RAL 2000                                       | Insulating material group             | IIIa                             |
| Comparative Tracking Index (CTI)      | ≥ 200                                          | UL 94 flammability rating             | V-0                              |
| Contact base material                 | CuSn                                           | Contact material                      | Cu-alloy                         |
| Contact surface                       | tinned                                         | Layer structure of solder connection  | 2...4 µm Ni / 5...8 µm Sn glossy |
| Layer structure of plug contact       | 2...4 undefined Ni / 5...8 undefined Sn glossy | Storage temperature, min.             | -40 °C                           |
| Storage temperature, max.             | 70 °C                                          | Operating temperature, min.           | -50 °C                           |
| Operating temperature, max.           | 100 °C                                         | Temperature range, installation, min. | -30 °C                           |
| Temperature range, installation, max. | 100 °C                                         |                                       |                                  |

## Rated data acc. to IEC

|                                                                       |                        |                                                                      |         |
|-----------------------------------------------------------------------|------------------------|----------------------------------------------------------------------|---------|
| tested acc. to standard                                               | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                        | 17 A    |
| Rated current, max. number of poles (Tu=20°C)                         | 12 A                   | Rated current, min. number of poles (Tu=40°C)                        | 14.5 A  |
| Rated current, max. number of poles (Tu=40°C)                         | 10 A                   | Rated voltage for surge voltage class / pollution degree II/2        | 320 V   |
| Rated voltage for surge voltage class / pollution degree III/2        | 160 V                  | Rated impulse voltage for surge voltage class/ pollution degree II/2 | 2,500 V |
| Rated impulse voltage for surge voltage class/ pollution degree III/2 | 2.5 kV                 |                                                                      |         |

## SL 3.50/08/90G 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Rated data acc. to CSA

Institute (CSA)



Certificate No. (CSA)

154685-1318353

Rated voltage (Use group B / CSA) 300 V

Rated voltage (Use group D / CSA) 300 V

Rated current (Use group B / CSA) 10 A

Rated current (Use group D / CSA) 10 A

Reference to approval values Specifications are maximum values, details - see approval certificate.

## Rated data acc. to UL 1059

Institute (UR)



Certificate No. (UR)

E60693

Rated voltage (Use group B / UL 1059) 300 V

Rated voltage (Use group D / UL 1059) 300 V

Rated current (Use group B / UL 1059) 10 A

Rated current (Use group D / UL 1059) 10 A

Reference to approval values Specifications are maximum values, details - see approval certificate.

## Packing

|           |       |            |        |
|-----------|-------|------------|--------|
| Packaging | Box   | VPE length | 115 mm |
| VPE width | 78 mm | VPE height | 53 mm  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002637    | ETIM 7.0    | EC002637    |
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 9.0  | 27-44-04-02 |
| ECLASS 9.1  | 27-44-04-02 | ECLASS 10.0 | 27-44-04-02 |
| ECLASS 11.0 | 27-46-02-01 | ECLASS 12.0 | 27-46-02-01 |
| ECLASS 13.0 | 27-46-02-01 | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## SL 3.50/08/90G 3.2SN OR BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|----------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Gold-plated contact surfaces on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |

## Approvals

Approvals



|                       |                                                                                                                                                                                                                                                                                                                                                         |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID       | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319226/-T1z1mm-S800/</a> <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/</a> |
| ROHS                  | Conform                                                                                                                                                                                                                                                                                                                                                 |
| UL File Number Search | UL Website                                                                                                                                                                                                                                                                                                                                              |
| Certificate No. (UR)  | E60693                                                                                                                                                                                                                                                                                                                                                  |

## Downloads

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Declaration of the Manufacturer</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Brochures                                   | <a href="#">FL DRIVES EN</a><br><a href="#">MB SMT EN</a><br><a href="#">FL DRIVES DE</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL BUILDING SAFETY EN</a><br><a href="#">FL APPL LED LIGHTING EN</a><br><a href="#">FL INDUSTR.CONTROLS EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL HEATING ELECTR EN</a><br><a href="#">FL APPL INVERTER EN</a><br><a href="#">FL BASE STATION EN</a><br><a href="#">FL ELEVATOR EN</a><br><a href="#">FL POWER SUPPLY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a><br><a href="#">PO OMNIMATE EN</a> |


## SL 3.50/08/90G 3.2SN OR BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Product image



## Dimensional drawing




The reproduction, distribution and utilization of this document as well as the communication of its contents to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. Weidmueller exclusively reserves the right to file for patents, utility models or designs.

© Weidmueller Interface GmbH & Co. KG

Dimensions without tolerances are no check dimensions

The English version is binding



hole pattern

P = 3.50 Raster Pitch

D = Ø1,3 +0.1  
Ø0.051" +0.1

d = 1,2mm oktagonale  
0.047" oktagonale

SHOWN: SL 3.50/04/90G

For the mounting of PCBs, it should be noted that the rated data given in the catalogue relates only to the connection elements. The necessary creepage and clearance paths must be observed in connection with the respective applicant in accordance with VDE 0110. The current-carrying capacity and pitch tolerance is to be determined according to DIN IEC 326 part 3 very fine.

Weidmueller connectors are tested to the DIN VDE 0627 standard, and are valid for its field of application. Provided that the connectors are used to the intended purpose, all requirements with respect to the occurring of electrical, mechanical, thermic and corrosive stress will be satisfied.

|                               |                        |
|-------------------------------|------------------------|
| 1,5                           | 0,1                    |
|                               | -0,3                   |
| 3,2                           | 0,1                    |
|                               | -0,3                   |
| 4,5                           | 0,1                    |
|                               | -0,3                   |
| pin length l/<br>Stiftlänge l | tolerance/<br>Toleranz |

|                           |      |                              |
|---------------------------|------|------------------------------|
| 24                        | 80.5 | +/-0.2                       |
| 23                        | 77.0 |                              |
| 22                        | 73.5 |                              |
| 21                        | 70.0 |                              |
| 20                        | 66.5 |                              |
| 19                        | 63.0 |                              |
| 18                        | 59.5 |                              |
| 17                        | 56.0 |                              |
| 16                        | 52.5 | +/-0.15                      |
| 15                        | 49.0 |                              |
| 14                        | 45.5 |                              |
| 13                        | 42.0 |                              |
| 12                        | 38.5 | +/-0.1                       |
| 11                        | 35.0 |                              |
| 10                        | 31.5 |                              |
| 9                         | 28.0 |                              |
| 8                         | 24.5 |                              |
| 7                         | 21.0 |                              |
| 6                         | 17.5 |                              |
| 5                         | 14.0 |                              |
| 4                         | 10.5 | Toleranz/<br>tolerance<br>L1 |
| 3                         | 7.0  |                              |
| 2                         | 3.5  |                              |
| n Polzahl/<br>no of poles | L1   | Toleranz/<br>tolerance<br>L1 |

|                                       |             |                              |          |                                                |            |  |
|---------------------------------------|-------------|------------------------------|----------|------------------------------------------------|------------|--|
| General tolerance:<br>DIN ISO 2768-mK |             | 96310/5<br>06.07.17 HELIS_MA |          | 00                                             | Cat.no.: . |  |
|                                       |             | Modification                 |          |                                                |            |  |
|                                       |             |                              |          |                                                |            |  |
|                                       | Drawn       | 21.08.2008                   | HELIS_MA | SL 3.50/.. /90...<br>STIFTLISTE<br>MALE HEADER |            |  |
|                                       | Responsible |                              | AMANN_A  |                                                |            |  |
|                                       | Checked     | 20.09.2017                   | HERTEL_S |                                                |            |  |
| Scale: 5/1                            | Approved    |                              | LANG_T   | Product file: SL 3.50                          |            |  |
| Supersedes: .                         |             |                              |          | 7296                                           |            |  |

## Recommended wave soldering profiles

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

### Single Wave:



### Double Wave:



### Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.